

DRC70-GKT

✓ ACTIVE


TE Internal #: DRC70-GKT

Gasket, Closed Cell Sponge, Black, -57 – 107 °C [-71 – 225 °F]

[View on TE.com >](#)



Connectors > Connector Accessories > Connector Seals & Cavity Plugs



Connector Seal & Plug Type: **Gasket**

Primary Product Material: **Closed Cell Sponge**

Primary Product Color: **Black**

Operating Temperature (Max): **107 °C [ 225 °F ]**

Contains Lubricant: **No**

Features

Industry Standards

UL Flammability Rating	UL 94HBF
------------------------	----------

Packaging Features

Packaging Method	Box
------------------	-----

Product Type Features

Connector Seal & Plug Type	Gasket
----------------------------	--------

Body Features

Primary Product Material	Closed Cell Sponge
Primary Product Color	Black

Usage Conditions

Operating Temperature (Max)	107 °C[225 °F]
Operating Temperature Range	-57 – 107 °C[-71 – 225 °F]

Other

Contains Lubricant	No
EU RoHS Compliance	Compliant
EU ELV Compliance	Compliant



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # DRC24-GKT  
GASKET, 24P, BLK, DRC16



TE Part # CAT-D799-CH8172  
DEUTSCH DRC Housings

Customers Also Bought

DRC70-GKT

Gasket, Closed Cell Sponge, Black, -57 – 107 °C [-71 – 225 °F]



TE Part #DRC40-GKT  
GASKET, 40P, BLK, DRC16

TE Part #CAT-D799-CH8172  
DEUTSCH DRC Housings

TE Part #DRC70-BT  
BOOT, 70P, 16SZ, PLG/REC, ST, BLK

TE Part #2-180916-0  
FF 250 TAB HSG 1P NYLON NAT

TE Part #0515-031-7005  
WIRE ROUTER, 70P, BLK, PLG

TE Part #0528-006-7005  
BKSHL, 70P, BLK, PLG, ST, SIDEAB, NW 26

Documents

Product Drawings

GASKET, 70P, BLK, DRC16

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_DRC70-GKT\_A.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_DRC70-GKT\_A.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_DRC70-GKT\_A.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

TERMINALS AND CONNECTORS

English

CONNECTOR SELECTOR

English

Product Specifications

Application Specification

English

DRC70-GKT

Gasket, Closed Cell Sponge, Black, -57 – 107 °C [-71 – 225 °F]

