



Pushing Performance
Since 1945

Han HV single module, 16A 2500V male




Image is for illustration purposes only. Please refer to product description.

Part number	09 14 002 3025
Specification	Han HV single module, 16A 2500V male
HARTING eCatalogue	https://b2b.harting.com/09140023025

Identification

Category	Modules
Series	Han-Modular®
Type of module	Han® HV module
Size of the module	Single module

Version

Termination method	Crimp termination
Gender	Male
Number of contacts	2
Details	Please order crimp contacts separately.
Pack contents	1 module 2 locking sleeves 2 heat shrink tubes

Technical characteristics

Conductor cross-section	0.14 ... 4 mm²
Wire outer diameter	≤5 mm
Rated current	16 A
Rated voltage	2,500 V
Rated impulse voltage	15 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C



Pushing Performance
Since 1945

Technical characteristics

Mating cycles	≥500
---------------	------

Material properties

Material (insert)	Polycarbonate / Teflon (PTFE)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	5dbb3851-b94e-4e88-97a1-571845975242
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

Specifications and approvals

Specifications	IEC 60664-1
	IEC 61984
	EN 50124-1
Approvals	DNV GL

Commercial data

Packaging size	1
Net weight	26.16 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140019867
ETIM	EC000438



Pushing Performance
Since 1945

Commercial data

eCl@ss

27440217 Module for industrial connectors (power/signals)