



Pushing Performance
Since 1945

Han M12 Crimp D-coded male met union nut



Image is for illustration purposes only. Please refer to product description.

Part number	09 14 881 1406
Specification	Han M12 Crimp D-coded male met union nut
HARTING eCatalogue	https://b2b.harting.com/09148811406

Identification

Category	Inserts
Series	Han-Modular®
Specification	With metal nut

Version

Termination method	Crimp termination
Gender	Male
Number of contacts	4
further contacts	+ shielding
Coding	D-coding
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.13 ... 0.82 mm²
Conductor cross-section [AWG]	AWG 26 ... AWG 18
Wire outer diameter	≤2.3 mm
Rated current	4 A
Rated voltage	32 V
Rated impulse voltage	0.8 kV
Pollution degree	3
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s



Pushing Performance
Since 1945

Technical characteristics

Insulation resistance	$>10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Contact resistance, shielding	$\leq 100 \text{ m}\Omega$
Tightening torque	0.6 Nm
Wrench size	12 13
Limiting temperature	-40 ... +85 °C
Mating cycles	≥ 500
Cable diameter	5.5 ... 8.7 mm

Material properties

Material (insert)	Liquid crystal polymer (LCP)
Material (shielding)	Copper alloy, nickel plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
----------------	--------------------------

Commercial data

Packaging size	1
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140187771
ETIM	EC000438
eCl@ss	27440205 Contact insert for industrial connectors