NEW

OMRON

Proximity Sensors

30 Years of Innovation

Long-distance Detection of Aluminum or Iron
A Proximity Sensor with a NEW Detection Principle












Smartclick Pre-wired Connector Models Standard Models






Aluminum Detection Distance: 1.5 to 2 Times Previous Models *In-house comparison of M18 Shielded Long-distance Models

Immunity against aluminum chips has enabled achieving long-distance detection of aluminum workpieces. The same detection distance has also been achieved for iron, allowing the E2V-X□ to be separated from workpieces made of either metal farther than any other Proximity Sensor.





Detection Made Visible


An operation indicator that is visible from any direction is provided as a standard feature.



Embeddable in Metal.

The first Long-distance Sensor that is shielded. Possible to be completely embedded in metal.

Embedded Mounting in Metal



Applications



Long-distance Detection of Crankshafts



Cylinder Block Seating Detection



Detect Passing Parts

Ordering Information

Standard-distance Sensors, DC 3-wire, Pre-wired Models (Standard Cable Length: 2 m)

Models with 5-m cables are also available and are ordered by adding "5M" to the end of the model number (e.g., E2V-X2B1 5M).

	Appearance		Canaina diatana	Otmt	Model		
			Sensing distance	Output	Operation mode NO	Operation mode NC	
		M12	2mm	PNP	E2V-X2B1	E2V-X2B2	
	W/4 01 1 1 1	IVITZ	2111111	NPN	E2V-X2C1	E2V-X2C2	
	Shielded	M18	Mao	5mm	PNP	E2V-X5B1	E2V-X5B2
		IVITO	Smin	NPN	E2V-X5C1	E2V-X5C2	
	1///1	M30	10mm	PNP	E2V-X10B1	E2V-X10B2	
		IVISO	TOTILIT	NPN	E2V-X10C1	E2V-X10C2	

Long-distance Sensors, DC 3-wire, Pre-wired Models (Standard Cable Length: 2 m)

Models with 5-m cables are also available and are ordered by adding "5M" to the end of the model number (e.g., E2V-X4B1 5M).

Appearance		Sensing distance Output		Model	
Appearance	Appearance		Output	Operation mode NO	Operation mode NC
	M12		PNP	E2V-X4B1	E2V-X4B2
Wat On the I	IVITZ	4mm	NPN	E2V-X4C1	E2V-X4C2
Shielded	M18	8mm	PNP	E2V-X8B1	E2V-X8B2
	IVITO	OHIII	NPN	E2V-X8C1	E2V-X8C2
1///	M30	15mm	PNP	E2V-X15B1	E2V-X15B2
	IVISU	Tomin	NPN	E2V-X15C1	E2V-X15C2

Long-distance Sensors, DC 3-wire, Connector Models

Appagrange		Consing distance	Output	Model	
Appearance		Sensing distance	Output	Operation mode NO	Operation mode NC
	M12	4 ma ma	PNP	E2V-X4B1-M1	E2V-X4B2-M1
V/// 01: 11 1	IVIIZ	4mm	NPN	E2V-X4C1-M1	E2V-X4C2-M1
Shielded	M18	0,000	PNP	E2V-X8B1-M1	E2V-X8B2-M1
	IVITO	8mm	NPN	E2V-X8C1-M1	E2V-X8C2-M1
12/21	Man	15,000	PNP	E2V-X15B1-M1	E2V-X15B2-M1
	M30	15mm	NPN	E2V-X15C1-M1	E2V-X15C2-M1

Long-distance Sensors, DC 3-wire, Smartclick Pre-wired Connector (M12) Models

Appearance		Sensing distance	Output	Model Operation mode NO
	M12	10		E2V-X4B1-M1TJ
V//4 Q1 : 1 1 1	IVIIZ	4mm	NPN	E2V-X4C1-M1TJ
Shielded	M18	8mm	PNP	E2V-X8B1-M1TJ
			NPN	E2V-X8C1-M1TJ
12/21	M30	15mm	PNP	E2V-X15B1-M1TJ
	IVIOU	15111111	NPN	E2V-X15C1-M1TJ

Standard "Twist-and-Click" Smartclick Connectors



Appearance	Туре	Cable length (m)	Model	Applicable Proximity Sensor Models
	Standard	2	XS5F-D421-D80-A	E2V-X□□□-M1/M1TJ
Smartclick	cable	5	XS5F-D421-G80-A	E2V-X□□□-M1/M1TJ
robo	Vibration-proof robot cable	2	XS5F-D421-D80-F	E2V-X□□□-M1/M1TJ
		5	XS5F-D421-G80-F	E2V-X□□□-M1/M1TJ
	Oil-resistant	2	XS5F-D421-D80-P	E2V-X□□□-M1/M1TJ
	polyurethane cable	5	XS5F-D421-G80-P	E2V-X□□□-M1/M1TJ

Ratings and Specifications

Size		M	12	М	18	M30			
Item Model		E2V-X2□□	E2V-X4□□	E2V-X5□□	E2V-X8□□	E2V-X10□□	E2V-X15□□		
Sensi	ng distance	2mm±10%	4mm±10%	5mm±10%	8mm±10%	10mm±10%	15mm±10%		
Set di	stance	0 to 1.6 mm	0 to 3.2 mm	0 to 4.0 mm	0 to 6.4 mm	0 to 8.0 mm	0 to 12.0 mm		
Differe	ential travel			10% max. of se	ensing distance				
Detec	table object	Ferrous metals and	non-ferrous metals (The s	ensing distance depends o	on the material of the sensi	ng object. Refer to Engine	ering Data (Typical).)		
Standa	rd sensing object	Aluminum: 12 × 12 × 3 mm	Aluminum: 12 × 12 × 3 mm	Aluminum: 18 × 18 × 3 mm	Aluminum: 24 × 24 × 3 mm	Aluminum: 30 × 30 × 3 mm	Aluminum: 45 × 45 × 3 mm		
Respoi	nse frequency*	150Hz	40Hz	70Hz	40Hz	70Hz	30Hz		
	supply voltage ing voltage range)			12 to 24 VDC (ripple (p-p)					
Currer	nt consumption		450 mW max. (C	urrent consumption: 15 r	mA max. at power supply	voltage of 30 V)			
Contro	OI Load current			Open-collector ou	tput, 100 mA max.				
output	t Residual voltage		2	V max. (Load current: 10	00 mA, Cable length: 2 n	า)			
Indica	itors	NO Models: C	peration indicator (yello	w) (flashing), Setting indi	cator (yellow) (lit); NC M	odels: Operation indicate	or (yellow) (lit)		
Operation mode			B1/C1 Models: NO (Refer to the timing charts under I/O Circuit Diagrams for details.)						
Protection circuits Power supply reverse			reverse polarity protect	ection, reversed output polarity protection, load short-circuit protection, surge suppressor					
Ambient temperature		Operating/Storage: –25 to 70°C (with no icing or condensation)							
Ambient humidity		Operating/Storage: 35% to 95% (with no condensation)							
Tempe	erature	Based on the sensing distance at 23°C in the temperature range of –25 to 70°C							
influer	nce	±10% max.	±15% max.	±10% max.	±15% max.	±10% max.	±15% max.		
Voltag	je influence	$\pm 1.5\%$ max. of sensing distance at rated voltage in the rated voltage $\pm 15\%$ range							
Insulat	tion resistance	50 $\text{M}\Omega$ min. (at 500 VDC) between current-carrying parts and case							
Dielec	ctric strength	1,000 VAC, 50/60 Hz for 1 minute between current-carrying parts and case							
Vibrat	ion resistance	Destruction: 10 to 55 Hz, 1.5-mm double amplitude for 2 hours each in X, Y, and Z directions							
Shock	resistance	Destruction: 1,000 m/s² 10 times each in X, Y, and Z directions							
Degre	e of protection	IEC IP67 (Pre-wired Models and Pre-wired Connector Models are oil-resistant to the OMRON in-house standard.)							
Conne	ection method	Pre-wired Model	s (Standard cable length	n: 2 m), Connector Mode	ls, Pre-wired Connector	Models (Standard cable	length: 300 mm)		
Weight	Cable	Approx	. 120 g	Approx. 150 g		Approx. 200 g			
(packed state)	Connector	Approx	k. 30 g	Approx. 45 g		Approx. 120 g			
siale)	Pre-wired Connector Models	Approx	k. 50 g	Approx. 70 g Approx. 140 g			. 140 g		
<u>0</u>	Case			Nickel-pla	ated brass				
eria	Sensing surface			Heat-resis	stant ABS				
Materials	Clamping nuts			Nickel-pla	ated brass				
_	Toothed washer			Zinc-pla	ated iron				
Acces	sories			Instructio	n manual				

^{*} The response frequency is an average value.

E2V-X2

Measurement conditions are as follows: Standard sensing object, a distance between target objects of twice the size of the standard sensing object, and a set distance of half the sensing distance.

E2V-X5


6.0 5.0 4.0


10 15 20 25 30 35 40

20 30

I/O Circuit Diagrams and Timing Charts

■ Output Circuit Diagrams and Connections





E2V-X□B□ (-M1/-M1TJ) Load Note: Connector Models NO Models: ①④③ NC Models: ①②③

Compatible Connector Cables: XS5F Series

M1: (2 1) M1TJ: (3 4)

Safety Precautions

⚠ WARNING

This product is not designed or rated for ensuring safety of persons. Do not use it for such purposes.




Never use the product with an AC power supply. Otherwise, explosion may result.



Engineering Data (Typical)

Side length of sensing object d (mm)


■ Influence of Sensing Object Size and Material



Side length of sensing object d (mm)


E2V-X4


■ Influence of Sensing Object Size and Material




Thickness of sensing object: t (mm)


E2V-X2









■ Sensing Area








Influence of Surrounding Metal

When embedding the Sensor in metal, be sure that the clearances given in the following table are maintained.



(Unit: mm) Table 1. Influence of Surrounding Metal E2V-X2 E2V-X5 E2V-X10 Model 0 d dia 12 18 30 D 0 0 0 m 12 24 45 27 45 n 18

Item Model	E2V-X4	E2V-X8	E2V-X15
Q	0	0	0 (See Note 1.)
d dia.	12	18	30 (See Note 1.)
D	0	0	0 (See Note 1.)
m	12	24	45
n	18	27	45

Note 1: If the thickness of the mounting bracket (t) exceeds 5 mm, be sure to install the Sensor so that $\ell \ge 2$, d (dia.) ≥ 45 , and D ≥ 2 .

Mutual Interference

When installing Sensors face-to-face or side-by-side, be sure that the minimum distances given in table 2 are maintained.




Chart 2. Mutual Interference			(Unit: mm)		
	Item Model	E2V-X2	E2V-X5	E2V-X10	
	Α	30	50	100	

Ь	20	30	50
Item Model	E2V-X4	E2V-X8	E2V-X15
Α	35	60	120
В	25	35	70

Other Information

Sensing Distance

- The sensing distance depends on the sensing object size, material, and thickness.
- If the sensing object has a thickness of less than 1 mm, the sensing distance will decrease.
- Use the following graph and the Influence of Sensing Object Size and Material information in Engineering Data (Typical) as a reference.

Connector Models


Aluminum and Iron Cuttings

Normally aluminum or iron cuttings will not be detected even if they adhere to or accumulate on the sensing surface. Detection signals may be output for the following. If this occurs, remove the cuttings from the sensing surface.

Diameter of cutting = d and diameter of sensing surface = D

Cuttings in center of sensing surface with $d \ge 2/3D$


Model Size D E2V-X2□/X4□ 10 E2V-X5□/X8□ 16 E2V-X10□/X15□ 28		(Unit: mm)
E2V-X5□/X8□ 16	Model Size	D
	E2V-X2□/X4□	10
E2V-X10□/X15□ 28	E2V-X5□/X8□	16
	E2V-X10□/X15□	28



Tightening Torque

Do not tighten the nut with excessive force.


A washer must be used with the nut.





Tightening	Par	t A	Part B
Model	Dimension(mm)	Torque	Torque
E2V-X2/X4	17	5.9N•m	9.8N•m
E2V-X5/X8	22	15N•m	45N•m
E2V-X10/X15	26	39N•m	78N•m

Dimensions

(Unit:mm)







Item Model	E2V-X4□-M1TJ	E2V-X8□-M1TJ	E2V-X15□-M1TJ
Α	M12×1	M18×1	M30×1.5
В	60	60	60
С		52	52
D	47	42	42
E	21 dia.	29 dia.	42 dia.
F	17	24	36
G	4	4	5

Mounting Hole Dimensions

}	Proximity Sensor dimensions	M12	M18	M30
	Dimension H (mm)	12.5 ^{+0.5} dia.	18.5 ^{+0.5} ₀ dia.	30.5 +0.5 dia.

This document provides information mainly for selecting suitable models. Please read the document Instruction Sheet carefully for information that the user must understand and accept before purchase, including information on warranty, limitations of liability, and precautions.

OMRON Corporation

Sensing Devices Division H.Q. Industrial Sensors Division Shiokoji Horikawa, Shimogyo-ku, Kyoto, 600-8530 Japan Tel: (81)75-344-7022 Fax: (81)75-344-7107

Regional Headquarters

OMRON EUROPE B.V. Sensor Business Unit Carl-Benz-Str. 4, D-71154 Nufringen, Germany Tel: (49) 7032-811-0/Fax: (49) 7032-811-199

OMRON ELECTRONICS LLC

One Commerce Drive Schaumburg, IL 60173-5302 U.S.A. Tel: (1) 847-843-7900/Fax: (1) 847-843-7787

OMRON ASIA PACIFIC PTE. LTD.

No. 438A Alexandra Road # 05-05/08 (Lobby 2), Alexandra Technopark, Singapore 119967 Tel: (65) 6835-3011/Fax: (65) 6835-2711

OMRON (CHINA) CO., LTD.

Room 2211, Bank of China Tower, 200 Yin Cheng Zhong Road, Pu Dong New Area, Shanghai, 200120, China Tel: (86) 21-5037-2222/Fax: (86) 21-5037-2200

Authorized Distributor:

Note: Specifications subject to change without notice.

Cat. No. D107-E1-01

Read and Understand This Catalog

Please read and understand this catalog before purchasing the products. Please consult your OMRON representative if you have any questions or comments

Warranty and Limitations of Liability

WARRANTY

OMRON's exclusive warranty is that the products are free from defects in materials and workmanship for a period of one year (or other period if specified) from date of sale by OMRON.

OMRON MAKES NO WARRANTY OR REPRESENTATION, EXPRESS OR IMPLIED, REGARDING NON-INFRINGEMENT, MERCHANTABILITY, OR FITNESS FOR PARTICULAR PURPOSE OF THE PRODUCTS. ANY BUYER OR USER ACKNOWLEDGES THAT THE BUYER OR USER ALONE HAS DETERMINED THAT THE PRODUCTS WILL SUITABLY MEET THE REQUIREMENTS OF THEIR INTENDED USE. OMRON DISCLAIMS ALL OTHER WARRANTIES, EXPRESS OR IMPLIED.

LIMITATIONS OF LIABILITY

OMRON SHALL NOT BE RESPONSIBLE FOR SPECIAL, INDIRECT, OR CONSEQUENTIAL DAMAGES, LOSS OF PROFITS, OR COMMERCIAL LOSS IN ANY WAY CONNECTED WITH THE PRODUCTS, WHETHER SUCH CLAIM IS BASED ON CONTRACT, WARRANTY, NEGLIGENCE, OR STRICT LIABILITY.

In no event shall responsibility of OMRON for any act exceed the individual price of the product on which liability is asserted.

IN NO EVENT SHALL OMRON BE RESPONSIBLE FOR WARRANTY, REPAIR, OR OTHER CLAIMS REGARDING THE PRODUCTS UNLESS OMRON'S ANALYSIS CONFIRMS THAT THE PRODUCTS WERE PROPERLY HANDLED, STORED, INSTALLED, AND MAINTAINED AND NOT SUBJECT TO CONTAMINATION, ABUSE, MISUSE, OR INAPPROPRIATE MODIFICATION OR REPAIR.

Application Considerations

SUITABILITY FOR USE

OMRON shall not be responsible for conformity with any standards, codes, or regulations that apply to the combination of products in the customer's application or use of the product.

At the customer's request, OMRON will provide applicable third party certification documents identifying ratings and limitations of use that apply to the products. This information by itself is not sufficient for a complete determination of the suitability of the products in combination with the end product, machine, system, or other application or use.

The following are some examples of applications for which particular attention must be given. This is not intended to be an exhaustive list of all possible uses of the products, nor is it intended to imply that the uses listed may be suitable for the products:

- Outdoor use, uses involving potential chemical contamination or electrical interference, or conditions or uses not described in this catalog.
- Nuclear energy control systems, combustion systems, railroad systems, aviation systems, medical equipment, amusement machines, vehicles, safety
 equipment, and installations subject to separate industry or government regulations.
- Systems, machines, and equipment that could present a risk to life or property.

Please know and observe all prohibitions of use applicable to the products.

NEVER USE THE PRODUCTS FOR AN APPLICATION INVOLVING SERIOUS RISK TO LIFE OR PROPERTY WITHOUT ENSURING THAT THE SYSTEM AS A WHOLE HAS BEEN DESIGNED TO ADDRESS THE RISKS, AND THAT THE OMRON PRODUCT IS PROPERLY RATED AND INSTALLED FOR THE INTENDED USE WITHIN THE OVERALL EQUIPMENT OR SYSTEM.

Disclaimers

CHANGE IN SPECIFICATIONS

Product specifications and accessories may be changed at any time based on improvements and other reasons.

It is our practice to change model numbers when published ratings or features are changed, or when significant construction changes are made. However, some specifications of the product may be changed without any notice. When in doubt, special model numbers may be assigned to fix or establish key specifications for your application on your request. Please consult with your OMRON representative at any time to confirm actual specifications of purchased product.

DIMENSIONS AND WEIGHTS

Dimensions and weights are nominal and are not to be used for manufacturing purposes, even when tolerances are shown.

ERRORS AND OMISSIONS

The information in this catalog has been carefully checked and is believed to be accurate; however, no responsibility is assumed for clerical, typographical, or proofreading errors, or omissions.

PERFORMANCE DATA

Performance data given in this catalog is provided as a guide for the user in determining suitability and does not constitute a warranty. It may represent the result of OMRON's test conditions, and the users must correlate it to actual application requirements. Actual performance is subject to the OMRON Warranty and Limitations of Liability.

PROGRAMMABLE PRODUCTS

OMRON shall not be responsible for the user's programming of a programmable product, or any consequence thereof.

COPYRIGHT AND COPY PERMISSION

This catalog shall not be copied for sales or promotions without permission.

This catalog is protected by copyright and is intended solely for use in conjunction with the product. Please notify us before copying or reproducing this catalog in any manner, for any other purpose. If copying or transmitting this catalog to another, please copy or transmit it in its entirety.

Cat. No. D107-E1-01

OMRON Corporation Industrial Automation Company

In the interest of product improvement, specifications are subject to change without notice.