



Identification & Labeling > Printable Tubing > RPS Commercial Grade Sleeves



Printable Tubing Type: **Ladder**

Printable Tubing Grade: **Commercial**

Shrink Ratio: **3:1**

Primary Product Color: **Yellow**

Markers per Sleeve: **1**

[All RPS Commercial Grade Sleeves \(57\)](#)

Features

Product Type Features

Printable Tubing Type	Ladder
Printable Tubing Grade	Commercial

Body Features

Shrink Ratio	3:1
Primary Product Color	Yellow
Markers per Sleeve	1

Dimensions

Product Length	16.94 mm[.667 in]
Expanded Inside Diameter (Min)	6.35 mm[.25 in]
Recovered Inside Diameter (Max)	2.11 mm[.083 in]
Compatible Cable Diameter Range	2.31 – 5.46 mm[.09 – .214 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Printer/Label Features

Printer Technology	Thermal Transfer
--------------------	------------------

Product Compliance



For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


TE Part # 1-2186501-1  
T3212-SWARE-PRINTER

TE Part # 1-2186502-1  
T3224-PRINTER

TE Part # 1-2186503-1  
T3224-SWARE-PRINTER

TE Part # 1-2186500-1  
T3212-PRINTER

Also in the Series | [RPS](#)



Printable Tubing(57)

Customers Also Bought

TE Part #ASCX003-1PN-050  
RECEPT ASSY 2 HOLE MTG AS SIZE 3  
COAX

TE Part #8779670001  
RPS-18-12/2.0-4

TE Part #2611893004  
44A9083-20-9

TE Part #2-1622825-4  
RL73K 3A R56 5% 1K RL

TE Part #1-1614782-5  
BDS 2 A 100 47R 10%

TE Part #ASCX603-1SN-050  
PLUG ASSY AS SIZE 3 COAX

TE Part #CF1638-000  
223W601-25-0

TE Part #2-1579008-1  
EXTRACTION TOOL

TE Part #0255970001  
RPS-5K-22-18/2.0-4

TE Part #3555830001  
RPS-8-4/2.0-4

Documents

Datasheets & Catalog Pages  
Cable Identification Product Shelf Life  
English

Product Specifications  
Product Specification  
English  
IDENTIFCATION PRINTER PRODUCT RIBBON MATRIX  
English



Instruction Sheets

Instruction Sheet (non U.S.)

English