



RPS

TE Internal #: 8375990001

Ladder, Commercial, 3:1, Yellow, 1 Markers per Sleeve, 50 mm [2 in]
Length, 12.7 mm [.5 in] Expanded Inside, RPS, Printable Tubing

[View on TE.com >](#)

Identification & Labeling > Printable Tubing > RPS Commercial Grade Sleeves



Printable Tubing Type: **Ladder**

Printable Tubing Grade: **Commercial**

Shrink Ratio: **3:1**

Primary Product Color: **Yellow**

Markers per Sleeve: **1**

[All RPS Commercial Grade Sleeves \(57\)](#)

Features

Product Type Features

Printable Tubing Type	Ladder
Printable Tubing Grade	Commercial

Body Features

Shrink Ratio	3:1
Primary Product Color	Yellow
Markers per Sleeve	1

Dimensions

Product Length	50 mm[2 in]
Expanded Inside Diameter (Min)	12.7 mm[.5 in]
Recovered Inside Diameter (Max)	4.22 mm[.166 in]
Compatible Cable Diameter Range	4.6 – 10.8 mm[.183 – .425 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Printer/Label Features

Printer Technology	Thermal Transfer
--------------------	------------------

Packaging Features



Packaging Quantity	1000
--------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2186501-1
T3212-SWARE-PRINTER



TE Part # 1-2186502-1
T3224-PRINTER




TE Part # 1-2186503-1
T3224-SWARE-PRINTER



TE Part # 1-2186500-1
T3212-PRINTER

Also in the Series | RPS



Printable Tubing(57)

Customers Also Bought



TE Part #193990-2
SKT ASSY,TYPE XII, #8 AWG



TE Part #5-963716-2
MQS0,63 Au tab LL unseal. 0,5-0,75



TE Part #SRK-BS-MD-ST-002
BKSHL, MED, BLK, ST, NW 22



TE Part #1622837-1
CRG0603 1% 120R




TE Part #1622350-1
LR1 1% 1K1



TE Part #3-1676913-5
YR1 0.1% 21K



TE Part #1-2371035-1
2POS,DIA 4MM,SOC HSG ASSY,SLD, COD A



TE Part #NB09952001
ATUM-19/6-0-STK



TE Part #2177058-1
INSULATION INSERT,180DEG



TE Part #2103124-4
HVA280 2P HEADER ASSY, KEY D

Documents

Datasheets & Catalog Pages

IDENTIFICATION SELECTION GUIDE

English

Cable Identification Product Shelf Life

English

Product Specifications

Product Specification

English



Instruction Sheets

Instruction Sheet (non U.S.)

English