



Part Number : [1300108049](#)

Product Description : Mini-Change A-Size
Double-Ended Cordset, 5 Poles, Male
(Straight) to Female (Straight), 16 AWG, Gray
TPU Cable, 15.0m (49.21') Length

Series Number : 130010

Status : Active

Product Category : Circular Industrial
Cordsets

Engineering Number : 115030B35M150



Documents & Resources

Drawings

[1300108049_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3; 10(a) per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2021)10043- DC (17 Jan 2022)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	130010
Description	Mini-Change A-Size Double-Ended Cordset, 5 Poles, Male (Straight) to Female (Straight), 16 AWG, Gray TPU Cable, 15.0m (49.21') Length
IP Rating	IP67
Product Name	Mini-Change
Type	Double Ended
UPC	887191594941

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	600V

Physical

Cable Diameter	8.50mm (.335")
Cable Length	15.0m (49.21')
Color - Cable Jacket	Gray
Connector End A	Mini-Change
Connector End B	Mini-Change
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	TPU

Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Electrophoretic Zinc Alloy
Material - Plating Mating	Gold
Net Weight	1919.434/g
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-40° to +90°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	16

This document was generated on Feb 25, 2025