




Passive Components > Resistors > Chassis Mount Resistors > Resistor Power BDS2A100



Resistor Type: **Power Resistor**

Resistance Class: **Up to 1kΩ**

Resistance Value: **220 Ω**

Power Rating: **100 W**

Element Type: **Thick Film**

[All Resistor Power BDS2A100 \(30\)](#)

Features

Product Type Features

Resistor Type	Power Resistor
Element Type	Thick Film

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Resistance Class	Up to 1kΩ
Resistance Value	220 Ω
Power Rating	100 W
Passive Component Tolerance	10 %

Termination Features

Number of Terminations	2
Chassis Mount Resistor Termination Type	Screw Terminals

Mechanical Attachment

Panel Mount Feature Type	Flange with Mounting Holes
--------------------------	----------------------------

Dimensions

Product Height	21 mm[.827 in]
Product Length	38 mm[1.496 in]



Product Width	25.5 mm[1.004 in]
---------------	-------------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C
Temperature Coefficient	±150 ppm/°C

Packaging Features

Packaging Method	Loose Piece - Tray
------------------	--------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

BDS2A100220RK

220 ohm Chassis Mount Resistor, 100 W, Thick Film, 2 Terminations, ±150 ppm/°C, 10 %, Screw Terminals, Loose Piece - Tray, CGS BDS





TE Part # CAT-C339-B349
Resistor Power BDS2A100



TE Part # 2-1614770-2
BDS 2 A 250 3R3 10%

Also in the Series | CGS BDS




Chassis Mount Resistors(150)


Customers Also Bought



TE Part #8-215083-6
MICRO-MATCH MOW.16P



TE Part #1958388-1
STRA,RCT,4,M5,NI



TE Part #282838-6
TERMI-BLOK PCB MOUNT 90 6P.



TE Part #2-1623773-0
C10 330R 5% (LOOSE)



TE Part #1622193-1
LR0204 1% 220K




TE Part #5-825433-0
PIN HEADER 50 P.



TE Part #36922
TERMINAL,SOLIS R 2/0 5/16



TE Part #382811-2
SHUNT, ECON, PHBR15 AU, BLUE



TE Part #872166001
DR-25-1/4-0-FAR-10M



TE Part #1337769-3
50 OHM COAX BNC STR PLUG STR P



Documents

Product Drawings

BDS 2 A 100 220R 10%

English

CAD Files

Customer View Model

ENG_CVM_CVM_1614782-8_J.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1614782-8_J.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1614782-8_J.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

4-1773460-6_RESISTIVE_SOLUTIONS_RAIL

English

1309350_PASSIVE_COMPONENT

English

Thick Film Power Resistors - Type BDS100 Series

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English