

# INSERTION THERMAL ENERGY METER

Field Adjustable, BACnet/Modbus® Outputs

CALIBRATION SERVICES AVAILABLE




IEFB-X-X-TXX

IEFB-X-X-TXX  
Shown with  
A-IEF-VLV-BR  
accessory valve

A-IEFB-THW-XX (2)

Hot-tap thermowells for model  
IEFB-X-X-RXX (2) shown  
with A-IEFB-VLV-BR-1  
accessory valve



A-IEFB-THW-XX (2) IEFB-X-X-RXX (2)

THERMOWELL MODEL CHART

Model	A	B
A-IEFB-THW-4	4-11/16" (119.0 mm)	5-25/32 (146.8 mm)
A-IEFB-THW-6	6-11/16" (169.8 mm)	7-25/32 (197.6 mm)

The **Series IEFB** is a field-adjustable insertion thermal energy meter that uses electromagnetic technology to accurately and reliably measure fluid velocity and energy consumption. The high accuracy IEFB is adjustable to fit pipe sizes from 4 to 10" (100 to 250 mm), while the standard accuracy IEFB fits pipe sizes 4 to 36" (100 to 900 mm). The energy meter is simple to install and incorporates a temperature meter and calculator into a single unit. The IEFB incorporates a temperature meter and a calculator into a single unit. The LCD display provides clear readings of the meter's values, including temperature and energy consumption, making it ideal for installation on chillers, boilers, and other heating and cooling applications. The high measuring accuracy and long lifetime keeps annual operating costs at a minimum. In addition, it offers several output options, including selectable BACnet MS/TP or Modbus® RTU communications protocol over 2-wire RS-485 and standard analog, frequency, and alarm outputs.

## FEATURES/BENEFITS

- Flexible, field configurable setup displays (-LCD integral option or remote accessory A-IEF-DSP) accommodate a variety of application configurations. Application information is display selectable and includes pipe size, pipe material, liquid type, analog output, pulse/frequency output, alarm outputs, communication, outputs, damping, and calibration factor
- High performance accuracy is maintained through changes in temperature, density and/or viscosity
- The Setup Wizard and installation tool are simple to use, providing quick and precise installation
- Accessory setup kit A-IEF-KIT comes with a thickness gage and measuring tape to ensure exact installation depth
- The meter has no moving parts and electrodes that discourage fouling, which gives the meter a long lifecycle and minimizes the need for maintenance
- Hot-tap isolation valve accessories allow for easy installation and removal in operational systems without system downtime

## APPLICATIONS

- Monitoring chiller cooling output performance
- Industrial boiler heating performance
- Energy efficiency monitoring
- Optimization of heat energy performance
- Commercial and residential heat energy consumption and metering
- District heating and cooling monitoring
- Energy cost allocation monitoring

## SPECIFICATIONS

**Service:** Compatible clean or dirty non coating, conductive liquids.

**Range:** 0 to 20 ft/s (0 to 6 m/s).\*

**Wetted Materials:** Body shaft/fitting: 316 SS; Electrodes: 316 SS; Electrode cap: Polymer/polystyrene; O-ring: Silicone; Thermowells: 304 SS.

**BTU Accuracy per EN1434/ASTM E3137/CSA C900.1-13:** High accuracy units: Class 2 for 2 to 20 ft/s (0.6 to 6 m/s)\*\*; Standard accuracy units: Class 3 for 6.5 to 20 ft/s (2 to 6 m/s)\*\*.

**Flow Sensor Accuracy:** High accuracy units:  $\pm 0.5\%$  of reading at calibrated velocity,  $\pm 1\%$  of reading from 2 to 20 ft/s (0.6 to 6 m/s)  $\pm 0.02$  ft/s ( $\pm 0.006$  m/s) at  $< 2$  ft/s (0.6 m/s); Standard accuracy units:  $\pm 1\%$  FS.

**Temperature Accuracy:** Class B  $\pm (0.30 + 0.005 \times t)^\circ\text{C}$  per EN60751.

**Differential Temperature Accuracy:**  $E_t = \pm (0.5 + 3 \times \Delta\theta_{\text{min}}/\Delta\theta) \%$  per EN1434.

**Calculator Accuracy:**  $E_c = \pm (0.5 + \Delta\theta_{\text{min}}/\Delta\theta) \%$  per EN1434.

**Temperature Compensation:** 140 to 220°F (60 to 104.4°C)  $< 2\%$  error over  $\pm 30^\circ\text{F}$  ( $\pm 1.1^\circ\text{C}$ ) change, 40 to 70°F (4.4 to 21.1°C)  $< 2\%$  error over  $\pm 10^\circ\text{F}$  ( $\pm 12.2^\circ\text{C}$ ) change.

**Temperature Limits:** Ambient: -20 to 160°F (-29 to 71°C)\*\*; LCD -4 to 158°F (-20 to 70°C); Process: 15 to 250°F (-9 to 121°C); Storage: -40 to 185°F (-40 to 85°C).

**Process Connection:** Flowmeter: 1" NPT or BSPT with accessory full port ball valve options; Thermowell: (2) 1/2" NPT or BSPT thermowell with 1" full port ball valve options.

**Pressure Limit:** 400 psi (27.6 bar) @ 100°F (37.8°C).

**Pressure Drop:**  $< 0.1$  psi at 12 ft/s in 4" ( $< 0.01$  bar at 3.7 m/s in 100 mm) and larger pipe.

**Outputs:** (1) Analog: 4-20 mA, 0-5 V, 0-10 V or 2-10 V (display selectable); (1) Pulse/Frequency: 0-15 V peak pulse, 0 to 500 Hz or scalable pulse output (display selectable); (2) Alarm: Empty pipe detection or minimum/maximum velocity, (display selectable) and reverse flow output indication.

**Power Requirements:** 12-42 VDC, .25 A @ 24 VDC; 12-36 VAC.

**Electrical Connection:** Removable terminal blocks, (2) model selectable 1/2" female NPT conduit connection, (2) PG 16 gland or (2) PG 16 gland with 10 ft (3 m) 9 conductor 22 AWG plenum rated cables, accessory cable lengths up to 200 ft (61 m) optional.

**Display (-LCD option):** 2 x 2" (50 x 50 mm) graphic LCD with backlight.

**Conductivity:**  $> 20$  microsiemens.

**Enclosure Material:** Powder coated die cast aluminum.

**Enclosure Ratings:** NEMA 6P (IP68) (Non display models); NEMA 4X (IP66) (-LCD option).

**Agency Approvals:** BTL.

## COMMUNICATIONS (-COM OPTION)

**Type:** BACnet MS/TP or Modbus® RTU communication protocol (default disabled, display selectable).

**Supported Baud Rates:** 9600, 19200, 38400, 57600, 76800, or 115200 bps (display selectable).

**Device Load:** 1/8 unit load.

## ADDITIONAL SPECIFICATIONS

**Applicable Pipe Material:** Most popular plastic and metal pipes; i.e. Carbon steel, SS, copper, UPVC/PVDF, galvanized steel, mild steel, and brass.

**Applicable Pipe Size:** 4 to 36" (100 to 900 mm), model dependent. See model chart.

**Diameter Length Requirements:**  $> 10$  upstream,  $> 5$  downstream.

**Temperature Resistance:** Matched 4 wire platinum RTD's.

**Relative Humidity:** 10 to 90% non-condensing.

**Output Impedance:** 4-20 mA: 536  $\Omega$ ; 5V: 500  $\Omega$ ; 10V: 1.27k  $\Omega$ .

\*For max flowrates  $> 10$  ft/s (3 m/s) order option -CC.

\*\*Verified at standard temperature 73.4°F (23°C) refer to listed standards for detailed accuracy formulations.

# INSERTION THERMAL ENERGY METER

Field Adjustable, BACnet/Modbus® Outputs

CALIBRATION SERVICES AVAILABLE

MODEL CHART									
Example	IEFB	-L	N	-CND	-R10	-LCD	IEFB-LN-CND-R10-LCD	Price	
Series	IEFB						Insertion thermal energy meter	\$2750.00	
Accuracy	L G S  F I E T H						Standard accuracy <10" (250 mm) pipe; 1% FS	-	
							Standard accuracy >10" (250 mm) pipe; 1% FS	-	
							Standard accuracy 4 to 36" (100 to 900 mm) pipe; 1% FS	+100.00	
							High accuracy 4" (100 mm) pipe; 1% of reading	+450.00	
							High accuracy 6" (150 mm) pipe; 1% of reading	+450.00	
Process Connection							High accuracy 8" (200 mm) pipe; 1% of reading	+450.00	
							High accuracy 10" (250 mm) pipe; 1% of reading	+450.00	
							High accuracy 4 to 10" (100 to 250 mm) pipe; 1% of reading	+2200.00	
							1" Male NPT	-	
							1" Male BSPT	-	
Housing							1/2" female NPT	-	
Electrical							PG 16 gland without cable	-	
Connection							PG 16 gland with (2) 10' (3 m) cables	-	
Temperature Sensors							(2) 10' (3 m) PT temperature sensors*	+20.00	
							(2) 20' (6 m) PT temperature sensors*	+80.00	
							(2) 50' (15 m) PT temperature sensors*	+100.00	
							(2) 10' (3 m) PT temperature sensors with hot-tap thermowells	+120.00	
							(2) 20' (6 m) PT temperature sensors with hot-tap thermowells	+180.00	
Options							(2) 50' (15 m) PT temperature sensors with hot-tap thermowells	+180.00	
							LCD	+250.00	
							COM	+300.00	
							NIST	+400.00 (N)	
							FC	+150.00 (N)	
Options							CC	+100.00	
							Custom configuration (required input)	-	

(N) Items are net priced and are not subject to any discount.

\*Thermowells not included. Refer to accessories model chart to purchase permanent thermowells.

Note: FOR MAXIMUM PERFORMANCE SELECT -LCD OPTION OR SETUP DISPLAY ACCESSORY.

ACCESSORIES		
Model	Description	Price
A-IEF-KIT	Setup kit (includes setup display, thickness gage, and measuring tape) and universal power adapter	\$1000.00
A-IEF-DSP	Setup display	550.00
A-IEF-VLV-BR†	1-1/4" full port isolation valve brass kit**	250.00
A-IEF-VLV-SS†	1-1/4" full port isolation valve 316 SS kit	500.00
Thermowells		
A-IEFB-THW-4	(2) 1/2" NPT, 4" thermowell for 4 to 7" pipe	\$25.00
A-IEFB-THW-6	(2) 1/2" NPT, 6" thermowell for ≥ 8" pipe	25.00
A-IEFB-THW-4-BSPT	(2) 1/2" BSPT, 4" thermowell for 4 to 7" pipe	25.00
A-IEFB-THW-6-BSPT	(2) 1/2" BSPT, 6" thermowell for ≥ 8" pipe	25.00
Hot-Tap Valves		
A-IEFB-VLV-BR-1†	(2) 1" NPT full port isolation valve brass for temperature sensor with 1" branch outlet and 1" nipple**	\$175.00
A-IEFB-VLV-SS-1†	(2) 1" NPT full port isolation valve 316 SS for temperature sensor with 1" branch outlet and 1" nipple	350.00

\*\*Brass fittings and pipe are not to be used with NSF Certified models. Brass valves are non-RoHS compliant. †BSPT valves also available

Modbus® is a registered trademark of Schneider Automation, Inc.

## SERIES A-IEF

# REMOTE DISPLAY FOR SERIES IEF AND IEFB

Convenient Access to IEF & IEFB Meter Readings



Flow Transmitters, Electromagnetic, Remote Display




Full functional display  
A-IEF-FDSP-RM

Indicator display  
A-IEF-IDSP-RM



Shown with IEF-HN-PG and  
A-IEF-VLV-BR accessory valve



The **Series A-IEF Remote Display** can be installed almost anywhere near a Series IEF flow transmitter or IEFB thermal energy meter. Both the indicator display (A-IEF-IDSP-RM) and the full functional display (A-IEF-FDSP-RM) have a maximum display cable length of 100 ft (30 m) to permit easy viewing of flow readings. The full functional display allows for convenient adjustment of configuration settings and allows the user to save the IEF or IEFB configuration settings to a computer for printing.

### FEATURES/BENEFITS

- Full functional display can be used to set up the IEF/IEFB and adjust the settings if it is installed in a hard-to-reach location.
- Indicator display makes it convenient to read process values if the meter is inaccessible.
- Varying cable lengths of up to 100 ft (30 m) allows for flexible installation on a wall or pipe mount.
- Easy to install and wire in the field.

### APPLICATIONS

- Mechanical rooms with a small footprint
- Hard-to-reach piping
- Boilers and chillers
- Chilled water
- Condenser water
- Make-up water
- Heating water
- Boiler feed water
- Steam condensate

### SPECIFICATIONS

**Temperature Limits:** Ambient: -4 to 158°F (-20 to 70°C); Storage: -40 to 185°F (-40 to 85°C).  
**Display:** 3.3" diagonal graphic LCD. Backlight (full functional display only).  
**Enclosure Material Housing:** Powder coated die cast aluminum.  
**Enclosure Rating:** NEMA 4X (IP66).  
**Electrical Connection:** Removable terminal blocks, #22 AWG (100 ft (30 m) max).  
**Mounting:** Wall or pipe mount.  
**Mounting Orientation:** Any orientation.  
**Weight:** 2.46 lbs (1.12kg).  
**Agency Approvals:** CE.

MODEL CHART		
Model	Description	Price
A-IEF-IDSP-RM	A-IEF-DSP-RM indicator remote display	\$500.00
A-IEF-FDSP-RM	A-IEF-DSP-RM full functional remote display	750.00

ACCESSORIES		
Model	Description	Price
A-IEF-CBL-50	Plenum rated cable 50 ft (15.2 m)	\$88.00

Modbus® is a registered trademark of Schneider Automation, Inc.