




Connectors > Socket Connectors > Memory Sockets > SIMM Sockets



Module Orientation: **Vertical**
Number of Positions: **72**
Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
-----------------------------------	-----------------------

Configuration Features

Number of Keys	1
Number of Rows	1
Module Orientation	Vertical
Number of Positions	72

Body Features

Retention Post Location	Center
Latch Plating Material	Nickel
Latch Material	Brass
Connector Profile	Standard

Contact Features

Contact Current Rating (Max)	1 A
Contact Underplating Material	Nickel
Contact Mating Area Plating Material	Tin (Sn)
Memory Socket Type	Memory Card



Contact Base Material	Phosphor Bronze
PCB Contact Termination Area Plating Material	Tin
	200 µin

Termination Features

Insertion Style	Cam-In
Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	3.05 mm, 3.66 mm[.12 in][.144 in]

Mechanical Attachment

Connector Mounting Type	Board Mount
Polarization	Right
Mating Alignment Type	Center Post

Housing Features

Housing Material	LCP (Liquid Crystal Polymer)
Housing Color	Natural
Centerline (Pitch)	1.27 mm[.05 in]

Dimensions

Center Retention Hole Diameter	1.63 mm[.064 in]
--------------------------------	------------------

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Box & Tube, Tube
Packaging Quantity	315

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant




China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1759503-1
mini PCI-E 8H Type I PKG G/F

Customers Also Bought




TE Part #1761681-5
IDC LOW PRO HDR 14P VERT HT
BLACK



TE Part #280390-1
2X8P MODU II SHRD HDR, RT ANG,
TIN



TE Part #1SNA199289R0200
DR2.5/8.N.ADO



TE Part #6-1676731-5
RN 0805 1K1 0.1% 5PPM 5K RL






TE Part #188826-4
31P.IEC-F FEM.CONN



TE Part #1-1393238-2
RTB14005



TE Part #1SNA199287R2000
DR2.5/8.ADO

TE Part #2205503-1
10/20P LATCH LEAD



TE Part #6-1676731-6
RN 0805 750R 0.1% 5PPM 5K RL

TE Part #1SNA199423R1000
FEAD2

Documents

Product Drawings

72 ME .050 VERT M/L PB-FREE

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5822021-4_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5822021-4_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5822021-4_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

MICRO-EDGE SIMM (Single In-Line Memory Module) Connectors

English