

Terminal Block **15xx RZ TP**

Replace "x" with 02 - 12 for number of poles.



Wire Range

- #10 - #22 AWG Copper Solid

Electrical Ratings

- Amps
 - 30 Amps (unprepared wire)
 - 75 Amps (when wired with crimp type ring, spade or fork terminal)
- 600 Volts AC/DC (UL 1059 Class C, User Group - General Industrial)
- Short Circuit Current Rated for 10,000 Amps
- Factory & Field Wiring
- Test point designed to accept meter leads with 4MM spring tip banana plug

Agency Compliance

- UL Recognized, UL 1059 Terminal Block Standard, File No. XCFR2.E62806
- CSA - certified to C22.2 No. 158, File No. LR19766
- CE compliant to IEC 60947-7-1
- RoHS Complaint

Material Information

- Connector: Brass, nickel plated
 - Insulator base:
 - Thermoplastic
 - Flammability rating of insulator base UL94V0
 - Insulator base temperature rating: -40°C to 125°C (UL RTI)
 - Terminal Screws: Plated Brass
 - Anchor screws: Steel, zinc plated
 - Test Ports: Plated Brass
-
- Marking Strips: Vinyl (White) are not provided and can be ordered seperately.

Termination Specifications


	Wire Range/ Terminal Type	Torque	Max Lug Width
	#10 - 22 AWG	20 in-lbs	N/A
	Listed Lug, Ring, Fork Terminals	20 in-lbs	.50"

- Total lug stack up: not to exceed 1/8" (.125")

Installation & Accessories

- Mounting
 - For use with #10 fastener
 - Recommended mounting torque not to exceed 25-30 in lbs
- Cover
 - Screw-On Clear cover: Thermoplastic, UL Recognized QMFZ2 - order CC 15XX (XX representing number of poles).
 - Snap-On Translucent Cover: Thermoplastic - Order CVR15XX (XX representing number of poles).
- Printed Marker Strips - Consult factory for custom printed applications (minimum order quantities of 1000 per custom print required)

Drawing



Catalog #	# of Poles	A	B
1502	2	2.00	1.63
1503	3	2.63	2.25
1504	4	3.25	2.88
1505	5	3.88	3.50
1506	6	4.50	4.12
1507	7	5.13	4.75
1508	8	5.75	5.38
1509	9	6.38	6.00
1510	10	7.00	6.63
1511	11	7.63	7.25
1512	12	8.25	7.88