



Connectors > Circular Connectors > Standard Circular Connectors



Sealable: No

Hermetically Sealed: No

Contacts Preloaded: No

Shielded: No

Mating Retention: Without

Features

Product Type Features

Sealable	No
----------	----

Configuration Features

Contacts Preloaded	No
--------------------	----

Body Features

Primary Product Color	Black
Environmental Protection	Without
Hermetically Sealed	No

Mechanical Attachment

Mating Alignment	Without
Mating Retention	Without

Operation/Application

Shielded	No
----------	----

Packaging Features

Packaging Quantity	1
--------------------	---



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



Also in the Series | NECTOR M Series



Connector Hardware(4)



PCB Headers & Receptacles(2)



Standard Circular Connectors(45)

Customers Also Bought

TE Part #293470-1
NECTOR M LOCKING FOR CTCs

TE Part #293469-1
NECTOR M PIN HSG FREE HANGING
CODE A

TE Part #1-2213266-2
NECTOR M PIN, CRIMP, 16-18 AWG

TE Part #1-2213265-2
NECTOR M SKT, CRIMP, 16-18 AWG

Documents

Product Drawings

NECTOR M CABLE NUT DIA 7.5-8.4MM

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-293607-1_G_c-1-293607-1-g.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-293607-1_G_c-1-293607-1-g.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-293607-1_G_c-1-293607-1-g.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Agency Approvals

Agency Approval Document

English

