




NOTE:

1.CABLE:USB2.0 UL2725 28AWG#1PR+22AWG#*2C+AEB 85% COLOR:BLACK
OD:4.5MM USB2.0
MARKING:BLACK BOX CORPORATION(←25.4mm→)E223178 兄 AWM STYLE 2725
80℃ 30V VW-1 USB Revision 2.0 C

2.CONNECTOR:USB A TYPE MALE TWO-PIECE WHITE RUBBER CORE
NICKEL-PLATED HOUSING

3.CONNECTOR:USB A TYPE FEMALE WELDED WIRE TYPE PLUG WHITE RUBBER
CORE NICKEL-PLATED HOUSING


4.PVC MOLDED COLOR:BLACK

5.LABEL:BLACK BOX P/N LABLE

ELECTRONIC TEST:

- A. OPEN/SHORT/INTERMITTENCE:100%.
 - B. CHARACTERISTIC IMPEDANCE:90±13.5Ω(TDR)
 - C. DIELECTRIC STRENGTH: AC-500V/MIN
 - D. INTRA-PAIR SKEW: 100ps/ CABLE
 - E. Contact Resistance: 3 ohm max
- ALL MATERIALS COMPLY WITH ROHS2(2015/863)

BBOX P/N	LENGTH
USB05E-0010	10FT



ELECTRONIC TEST:

- A. OPEN/SHORT/INTERMITTENCE:100%.
 - B. CHARACTERISTIC IMPEDANCE:90±13.5Ω(TDR)
 - C. DIELECTRIC STRENGTH: AC-500V/MIN
 - D. INTRA-PAIR SKEW: 100ps/ CABLE
 - E. Contact Resistance: 3 ohm max
- ALL MATERIALS COMPLY WITH ROHS2(2015/863)

BLACK BOX					
Tolerance:		APPROVED BY:			
X	±				
.X	±	CHECK BY: George Liu		USB05E-0010-R2	
.XX	±				
.XXX	±	DRAWN BY: Dong.MI		Description: USB2.0 AM to AF Cable	
Angel:		DATE: 2023.09.12		DWG. NO:	
X	±				
.X	±	Scale:	Unit mm	SHEET: 1 OF 1	REV: 0

REV	ECN NO	DESCRIPTION	APPD.	DATE
-----	--------	-------------	-------	------