



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **4**

Centerline (Pitch): **2.5 mm [.098 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	4
Number of Rows	1

Electrical Characteristics

Operating Voltage	350 VDC
Insulation Resistance	500 MΩ

Body Features

Connector Profile	Standard
Primary Product Color	Natural

Contact Features



Contact Layout	Inline
Contact Type	Socket
Contact Current Rating (Max)	2 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	Without
Mating Retention Type	Lock
PCB Mount Retention	Without
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon 6/6
Housing Entry Configuration	Both Ends Closed
Centerline (Pitch)	2.5 mm[.098 in]

Dimensions

Connector Height	5.75 mm
Connector Length	14 mm

Usage Conditions

Operating Temperature Range	-20 – 95 °C[-4 – 203 °F]
-----------------------------	--------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Compatible With Agency/Standards Products	UL
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Bag
Packaging Quantity	1000

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Melamine (3% in Component Part) Article Safe Usage Statements: Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 170262-4
EIS CONNECTOR FORMING



TE Part # 170204-1
EIS RECPT CONTACT



TE Part # 170204-4
170262-4 LP E1CRIMP SNAP IN



TE Part # 172732-4
POST HEADER 4P EIS WITH KINK



TE Part # 171826-4
POST HEADER ASSY HORIZONTAL EI



TE Part # 176153-4
EIS POST HDR ASSY H 4P GOLD



TE Part # 170263-2
E.I.S. CONTACT



TE Part # 170204-2
EIS CONTACT



TE Part # 170205-2
E.I. SERIES CONTACT LP



TE Part # 170263-3
EIS CONNCTOR FORMING



TE Part # 171825-4
TYPE V EIS CONNECTOR 4P ASSY



TE Part # 172213-4
EIS CAP HSG PANEL MOUNT 4P NATUTURAL



TE Part # 170262-1
EIS CONTACT



TE Part # 170262-2
EIS CONTACT



TE Part # 173081-4
4P EIS POST HDR ASSY



TE Part # 170263-1
EIS CONTACT



TE Part # 172107-4
H-TYPE E.I.S. CONN. 4P ASSY



TE Part # 177537-4
2.5 M.I.S POST HDR ASSY 4P



TE Part # 170205-3
EIS CONTACT LP



TE Part # 172106-4
V-TYPE E.I.S. CONN. 4P ASSY

Customers Also Bought



TE Part #171822-5
EIS REC. HSG 5P-NATURAL



TE Part #171822-9
EIS REC. HSG 9P-NATURAL



TE Part #172211-3
EIS CAP HSG FREE HANG 3P NATUTURAL



TE Part #171822-8
EIS REC. HSG 8P-NATURAL






TE Part #1-171822-0
EIS REC. HSG 10P-NATURAL



TE Part #172211-2
EIS CAP HSG FREE HANG 2P NATUTURAL



TE Part #172211-6
EIS CAP HSG FREE HANG 6P NATUTURAL



TE Part #170429-1
EIS REC CONT 26-20 AWG BR TN



TE Part #172211-4
EIS CAP HSG FREE HANG 4P NATUTURAL

TE Part #811698-SF
FN9264-10-06

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_171822-4_R.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_171822-4_R.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_171822-4_R.3d_stp.zip

English

Customer View Model

ENG_CVM_171822-4_L.3d_igs.zip

English

Customer View Model

ENG_CVM_171822-4_L.3d_stp.zip

English

Customer View Model

ENG_CVM_171822-4_L.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1-1773972-5_EIS_Connectors_Brochure



English

Product Specifications

Crimping of AMP EI Series Connector Contacts

Japanese

Application Specification

Japanese

Agency Approvals

Agency Approval Document

English