



Product: [9842](#)

RS485, 2 Pr #24 Str TC, PE Ins, OS+TC Brd, PVC Jkt, CM

Product Description

RS-485, 2 Pair 24AWG (7x32) Tinned Copper, PE Insulation, Overall Beldfoil®+Tinned Copper Braid(90%) Shield, PVC Outer Jacket, CM

Technical Specifications

Product Overview

| | |
|------------------------|--|
| Suitable Applications: | RS-485, POS; Computer communications; Low Voltage Analog Signals (4-20ma, 0-10v, ...); Low Voltage Digital Control (24v, ...); Line Level Audio; Panel Wiring; serial communication (RS-485 standard) comprising of PLCs, VFDs, HMI's, motors, RTU, SCADA, etc. within noisy environments over long distance, etc. |
|------------------------|--|

Construction Details

Conductor

| Element | No. of Elements | Size | Stranding | Material |
|---------|-----------------|--------|-----------|--------------------|
| Pair(s) | 2 | 24 AWG | 7x32 | TC - Tinned Copper |

Insulation

| Element | Material | Nom. Thickness | Nom. Insulation Diameter | Color Code |
|---------|-------------------|--------------------|--------------------------|--|
| Pair(s) | PE - Polyethylene | 0.022 in (0.56 mm) | 0.068 in (1.7 mm) | White/Blue Stripe & Blue/White Stripe, White/Orange Stripe & Orange/White Stripe |

Outer Shield

| Shield Type | Material | Coverage | Drainwire Type |
|-------------|-------------------------|----------|------------------|
| Tape | Bi-Laminate (Alum+Poly) | 100% | 24 AWG (7x32) TC |
| Braid | Tinned Copper (TC) | 90% | |

Outer Jacket

| Material | Nom. Thickness | Nom. Diameter |
|--------------------------|--------------------|--------------------|
| PVC - Polyvinyl Chloride | 0.035 in (0.89 mm) | 0.340 in (8.64 mm) |

| | |
|-----------------------------------|---------------------|
| Table Notes: | Jacket OD +/- 0.025 |
| Overall Cable Diameter (Nominal): | 0.340 in (8.64 mm) |

Electrical Characteristics

Electricals

| Element | Nom. Conductor DCR | Nom. Capacitance Cond-to-Cond | Nom. Capacitance Cond-to-Other (Conds + Shield) | Nom. Characteristic Impedence | Nom. Velocity of Prop. | Max. Current |
|---------|--------------------|-------------------------------|---|-------------------------------|------------------------|--------------------------------|
| Pair(s) | 24 Ohm/1000ft | 12.8 pF/ft (42.0 pF/m) | 23 pF/ft | 120 Ohm | 66% | 2.1 Amps per Conductor at 25°C |

| | |
|------------------------|-----------------------------|
| Nom. Outer Shield DCR: | 2.2 Ohm/1000ft (7.2 Ohm/km) |
|------------------------|-----------------------------|

High Frequency (Nominal/Typical)

| Element | Frequency [MHz] | Nom. Insertion Loss (Attenuation) |
|---------|-----------------|-----------------------------------|
| Pair(s) | 1 | 0.6 dB/100ft |

Voltage

| UL Voltage Rating |
|--------------------------------|
| 300 V (CM), 30 V (UL AWM 2919) |

Mechanical Characteristics

Temperature

| UL Temperature | Operating |
|----------------|----------------|
| 80°C | -30°C to +80°C |

Bend Radius

| Stationary Min. | Installation Min. |
|-----------------|-------------------|
| 3.5 in (89 mm) | 3.5 in (89 mm) |

| | |
|--------------------|----------------|
| Max. Pull Tension: | 87 lbs (39 kg) |
| Bulk Cable Weight: | 49 lbs/1000ft |

Standards and Compliance

| | |
|----------------------------------|---|
| Environmental Suitability: | Indoor |
| Flammability / Reaction to Fire: | UL 1685 UL Loading, IEC 60332-1-2 |
| CPR Compliance: | CPR Euroclass: Eca; CPR UKCA Class: Eca |
| NEC / UL Compliance: | Article 800, CM |
| AWM Compliance: | AWM 2919 |
| CEC / C(UL) Compliance: | CM |
| European Directive Compliance: | EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE) |
| UK Regulation Compliance: | UKCA Mark |
| APAC Compliance: | China RoHS II (GB/T 26572-2011) |
| Other Standard Compliance(s): | DMX-512 |
| Plenum Number: | 82842, 89842 |
| Non-Plenum Number: | 9841ZH |

History

| | |
|----------------------|--|
| Update and Revision: | Revision Number: 0.606 Revision Date: 12-22-2023 |
|----------------------|--|

Part Numbers

Variants

| Item # | Color | Putup Type | Length | UPC/EAN | Footnote |
|---------------|--------|------------|-----------|---------------|----------|
| 9842.0030 | Chrome | Reel | 30 m | 8719605023001 | |
| 9842 060100 | Chrome | Reel | 100 ft | 612825259510 | |
| 9842.009999 | Chrome | Reel | 151 m | 8719605023032 | |
| 9842.00152 | Chrome | Reel | 152 m | 8719605022981 | |
| 9842.00305 | Chrome | Reel | 305 m | 8719605023018 | |
| 9842 060500 | Chrome | Reel | 500 ft | 612825259541 | C |
| 9842.00500 | Chrome | Reel | 500 m | 8719605023025 | |
| 9842 0601000 | Chrome | Reel | 1,000 ft | 612825259527 | C |
| 9842.001000 | Chrome | Reel | 1,000 m | 8719605022974 | |
| 9842.001525 | Chrome | Reel | 1,525 m | 8719605022998 | |
| 9842 0605000 | Chrome | Reel | 5,000 ft | 612825259558 | |
| 9842 06010000 | Chrome | Reel | 10,000 ft | 612825259534 | |

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.