



The DNA of tech.™

# Product Termination Notification

Product Group: SIL/Thursday February 13, 2025/PTN-SIL-009-2025-REV-0



## Conversion to Copper (Cu) Wire – SQ2301ES

For further information, please contact your regional Vishay office.

### CONTACT INFORMATION

#### Americas

Vishay Siliconix  
2565 Junction Ave  
-  
San Jose CA United States 95134  
Phone: (408) 988-8000  
Fax:  
automostechsupport@vishay.com

#### Europe

Vishay Electronic GmbH  
Dr.-Felix-Zandman-Platz 1  
-  
Selb Germany 95100  
Phone: 49-9287-71 0  
Fax: 49-9287-70435  
business-europe@vishay.com

#### Asia

Vishay Intertechnology Asia Pte. Ltd  
37A Tampines Street 92 #07-01  
-  
Singapore Singapore 528886  
Phone: 65 6788 6668  
Fax: 65 6788 0988  
business-asia@vishay.com

**Description of Change:** The affected part number listed in this notification will be converted to a Copper wire material set. The new ordering code is SQ2301ES-T1\_GE3 which has Identical silicon technology and silicon die design as SQ2301CES. Small changes to the data sheet AC parameters are a consequence of lot to lot variation and/or updated characterization methods (reference: SQ2301CES Doc # 62454 Rev. A). Device performance in the application will not be impacted. There will be no change to the wafer fab location.

**Reason for Change:** None

**Expected Influence on Quality/Reliability/Performance:** Standardization of materials

**Part Numbers/Series/Families Affected:** SQ2301ES-T1\_GE3

**Vishay Brand(S):** Vishay Siliconix

#### Time Schedule:

Last Time Buy Date: Thursday August 14, 2025

Last Time Ship Date: Monday February 16, 2026

**Sample Availability:** Qualified samples of replacement product are available on request.

**Product Identification:** SQ2301CES-T1\_GE3

**Qualification Data:** AEC Q101 qualification data of replacement product is available. Qualification PPAP is available on request.


**This PTN is considered approved, without further notification, unless we receive specific customer concerns before Thursday August 14, 2025 or as specified by contract.**

**Issued By:** Lance Gurrola, automostechsupport@vishay.com



## Automotive P-Channel 20 V (D-S) 175 °C MOSFET

SOT-23 (TO-236)




### FEATURES

- TrenchFET® power MOSFET
- AEC-Q101 qualified
- 100 %  $R_g$  and UIS tested
- Material categorization:  
for definitions of compliance please see  
[www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT  
**HALOGEN**  
**FREE**



PRODUCT SUMMARY	
$V_{DS}$ (V)	-20
$R_{DS(on)}$ ( $\Omega$ ) at $V_{GS} = -4.5$ V	0.120
$R_{DS(on)}$ ( $\Omega$ ) at $V_{GS} = -2.5$ V	0.180
$I_D$ (A)	-3.9
Configuration	Single

ORDERING INFORMATION	
Package	SOT-23
Lead (Pb)-free and halogen-free	SQ2301CES (for detailed order number please see <a href="http://www.vishay.com/doc?79771">www.vishay.com/doc?79771</a> )

ABSOLUTE MAXIMUM RATINGS ( $T_C = 25$ °C, unless otherwise noted)				
PARAMETER		SYMBOL	LIMIT	UNIT
Drain-source voltage		$V_{DS}$	-20	V
Gate-source voltage		$V_{GS}$	$\pm 8$	
Continuous drain current	$T_C = 25$ °C	$I_D$	-3.9	A
	$T_C = 125$ °C		-2.2	
Continuous source current (diode conduction)		$I_S$	-3.7	
Pulsed drain current <sup>a</sup>		$I_{DM}$	-15	
Single pulse avalanche current		$I_{AS}$	-9	
Single pulse avalanche energy	L = 0.1 mH	$E_{AS}$	4	mJ
Maximum power dissipation	$T_C = 25$ °C	$P_D$	3	W
	$T_C = 125$ °C		1	
Operating junction and storage temperature range		$T_J, T_{stg}$	-55 to + 175	°C

THERMAL RESISTANCE RATINGS				
PARAMETER		SYMBOL	LIMIT	UNIT
Junction-to-ambient	PCB mount <sup>c</sup>	$R_{thJA}$	166	°C/W
Junction-to-case (drain)		$R_{thJF}$	50	

### Notes

- Package limited
- Pulse test; pulse width  $\leq 300$   $\mu$ s, duty cycle  $\leq 2$  %
- When mounted on 1" square PCB (FR-4 material)



SPECIFICATIONS (T <sub>C</sub> = 25 °C, unless otherwise noted)							
PARAMETER	SYMBOL	TEST CONDITIONS		MIN.	TYP.	MAX.	UNIT
Static							
Drain-source breakdown voltage	V <sub>DS</sub>	V <sub>GS</sub> = 0, I <sub>D</sub> = -250 μA		-20	-	-	V
Gate-source threshold voltage	V <sub>GS(th)</sub>	V <sub>DS</sub> = V <sub>GS</sub> , I <sub>D</sub> = -250 μA		-0.45	-	-1.5	
Gate-source leakage	I <sub>GSS</sub>	V <sub>DS</sub> = 0 V, V <sub>GS</sub> = ± 8 V		-	-	± 100	nA
Zero gate voltage drain current	I <sub>DSS</sub>	V <sub>GS</sub> = 0 V	V <sub>DS</sub> = -20 V	-	-	-1	μA
		V <sub>GS</sub> = 0 V	V <sub>DS</sub> = -20 V, T <sub>J</sub> = 125 °C	-	-	-50	
		V <sub>GS</sub> = 0 V	V <sub>DS</sub> = -20 V, T <sub>J</sub> = 175 °C	-	-	-150	
On-state drain current <sup>a</sup>	I <sub>D(on)</sub>	V <sub>GS</sub> = -4.5 V	V <sub>DS</sub> ≥ 5 V	-8	-	-	A
Drain-source on-state resistance <sup>a</sup>	R <sub>DS(on)</sub>	V <sub>GS</sub> = -4.5 V	I <sub>D</sub> = -2.8 A	-	0.080	0.120	Ω
		V <sub>GS</sub> = -2.5 V	I <sub>D</sub> = -2 A	-	0.110	0.180	
Forward transconductance <sup>a</sup>	g <sub>fs</sub>	V <sub>DS</sub> = -1.6 V, I <sub>D</sub> = -2.8 A		-	7	-	S
Dynamic <sup>b</sup>							
Input capacitance	C <sub>iss</sub>	V <sub>GS</sub> = 0 V	V <sub>DS</sub> = -10 V, f = 1 MHz	-	369	425	pF
Output capacitance	C <sub>oss</sub>			-	91	100	
Reverse transfer capacitance	C <sub>rss</sub>			-	64	70	
Total gate charge <sup>c</sup>	Q <sub>g</sub>	V <sub>GS</sub> = -4.5 V	V <sub>DS</sub> = -10 V, I <sub>D</sub> = -2.8 A	-	5.4	8	nC
Gate-source charge <sup>c</sup>	Q <sub>gs</sub>			-	0.81	-	
Gate-drain charge <sup>c</sup>	Q <sub>gd</sub>			-	1.75	-	
Gate resistance	R <sub>g</sub>	f = 1 MHz		3	6	14.5	Ω
Turn-on delay time <sup>c</sup>	t <sub>d(on)</sub>	V <sub>DD</sub> = -10 V, R <sub>L</sub> = 10 Ω I <sub>D</sub> ≡ -1 A, V <sub>GEN</sub> = -4.5 V, R <sub>g</sub> = 1 Ω		-	10	22	ns
Rise time <sup>c</sup>	t <sub>r</sub>			-	17	21	
Turn-off delay time <sup>c</sup>	t <sub>d(off)</sub>			-	23	45	
Fall time <sup>c</sup>	t <sub>f</sub>			-	9	15	
Source-Drain Diode Ratings and Characteristics <sup>b</sup>							
Pulsed current <sup>a</sup>	I <sub>SM</sub>			-	-	-15	A
Forward voltage	V <sub>SD</sub>	I <sub>F</sub> = -1.6 A, V <sub>GS</sub> = 0		-	-0.8	-1.2	V
Body diode reverse recovery time	t <sub>rr</sub>	I <sub>F</sub> = -1.2 A, di/dt = 100 A/μs		-	15	30	ns
Body diode reverse recovery charge	Q <sub>rr</sub>			-	6.5	13	nC
Reverse recovery fall time	t <sub>a</sub>			-	6	-	ns
Reverse recovery rise time	t <sub>b</sub>			-	9	-	
Body diode peak reverse recovery current	I <sub>RM(REC)</sub>			-	-1	-	A


**Notes**

- a. Pulse test; pulse width  $\leq 300\text{ }\mu\text{s}$ , duty cycle  $\leq 2\%$   
b. Guaranteed by design, not subject to production testing  
c. Independent of operating temperature


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.




**TYPICAL CHARACTERISTICS** ( $T_A = 25\text{ }^{\circ}\text{C}$ , unless otherwise noted)




**Output Characteristics**




**Transfer Characteristics**




**Transconductance**



**On-Resistance vs. Drain Current**




**Capacitance**




**Gate Charge**




**TYPICAL CHARACTERISTICS** ( $T_A = 25\text{ }^{\circ}\text{C}$ , unless otherwise noted)




**On-Resistance vs. Junction Temperature**




**Source-Drain Diode Forward Voltage**



**On-Resistance vs. Gate-to-Source Voltage**




**Threshold Voltage**




**Drain Source Breakdown vs. Junction Temperature**



**THERMAL RATINGS** ( $T_A = 25\text{ }^{\circ}\text{C}$ , unless otherwise noted)




**Safe Operating Area**



**Normalized Thermal Transient Impedance, Junction-to-Foot**



**THERMAL RATINGS** ( $T_A = 25\text{ }^{\circ}\text{C}$ , unless otherwise noted)



**Normalized Thermal Transient Impedance, Junction-to-Ambient**

**Note**

- The characteristics shown in the two graphs
  - Normalized Transient Thermal Impedance Junction-to-Ambient ( $25\text{ }^{\circ}\text{C}$ )
  - Normalized Transient Thermal Impedance Junction-to-Foot ( $25\text{ }^{\circ}\text{C}$ )are given for general guidelines only to enable the user to get a “ball park” indication of part capabilities. The data are extracted from single pulse transient thermal impedance characteristics which are developed from empirical measurements. The latter is valid for the part mounted on printed circuit board - FR4, size 1" x 1" x 0.062", double sided with 2 oz. copper, 100 % on both sides. The part capabilities can widely vary depending on actual application parameters and operating conditions

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see [www.vishay.com/ppg?62454](http://www.vishay.com/ppg?62454).



### Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.