

Sound Module, Harmony XVB7 Modular Tower Light, Ø70mm, 2 Tones, Grey

XVB7C9S

Product availability: Stock - Normally stocked in distribution facility

Main

| Range of Product | Harmony XVB7 | |
|---------------------------|---|--|
| Product or Component Type | Sound module | |
| Device Composition | 2 tone buzzer | |
| Device short name | XVB7 | |
| Mounting diameter | 2.8 in (70 mm) | |
| Signalling type | Continuous or intermittent buzzer 2 tones | |
| Material | Polycarbonate | |
| Housing Colour | Dark grey | |
| Net Weight | 0.176 lb(US) (0.080 kg) | |
| Mounting position | Upright/inverted | |

Complementary

| Noise level | 88102 dB 1 m | | |
|--|--------------------------------|--|--|
| Pulse frequency | 1 Hz | | |
| Control Type | DIP switch for tone/loudness | | |
| [Ue] rated operational voltage | 24 V AC/DC | | |
| Rated operational voltage limits | 21.626.4 V AC/DC | | |
| Current consumption | 33 mA 24 V AC 22 mA 24 V DC | | |
| Inrush current | 1 A | | |
| Electrical shock protection class | Class II | | |
| [Ui] rated insulation voltage | 50 V | | |
| [Uimp] rated impulse withstand voltage | 0.5 kV | | |

Environment

| pollution degree | 2 | |
|---------------------------------------|---------------------------------------|--|
| Ambient air temperature for operation | -13140 °F (-2560 °C) | |
| Ambient Air Temperature for Storage | -40158 °F (-4070 °C) | |
| IP degree of protection | IP66 | |
| Environmental Type ratings | Type 4/4X/12/13 indoor use only | |
| Vibration resistance | 6 gn +/- 0.5 mm 10500 Hz)in operation | |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Shock resistance | 30 gn 6 ms) in operation | |
|------------------------|---|--|
| Standards | UL 60947-5-1 IEC 60947-5-1 CSA C22.2 No 60947-5-1 | |
| Product Certifications | cULus CCC RCM UKCA CE | |

Ordering and shipping details

| Category | US100XV22612 |
|-------------------|---------------|
| Discount Schedule | 00XV |
| GTIN | 3606487129615 |
| Returnability | Yes |
| Country of origin | FR |

Packing Units

| Unit Type of Package 1 | PCE | |
|------------------------------|--------------------------|--|
| Number of Units in Package 1 | 1 | |
| Package 1 Height | 2.56 in (6.500 cm) | |
| Package 1 Width | 2.87 in (7.300 cm) | |
| Package 1 Length | 2.87 in (7.300 cm) | |
| Package 1 Weight | 2.822 oz (80.000 g) | |
| Unit Type of Package 2 | S03 | |
| Number of Units in Package 2 | 60 | |
| Package 2 Height | 11.81 in (30.000 cm) | |
| Package 2 Width | 11.81 in (30.000 cm) | |
| Package 2 Length | 15.75 in (40.000 cm) | |
| Package 2 Weight | 11.618 lb(US) (5.270 kg) | |



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

| ∇ Environmental footprint | |
|--|-------------------------------|
| Carbon footprint (kg CO2 eq, Total Life cycle) | 7 |
| Environmental Disclosure | Product Environmental Profile |

Use Better

| Packaging made with recycled cardboard | No |
|--|---|
| Packaging without single use plastic | No |
| EU RoHS Directive | Compliant with Exemptions |
| REACh Regulation | REACh Declaration |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |


Use Again

| ○ Repack and remanufacture | |
|----------------------------|--|
| Circularity Profile | End of Life Information |
| Take-back | No |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

XVB7C9S


Dimensions Drawings

Dimensions



Mounting and Clearance

Mounting Overview



Product data sheet

| A1, A6, A11 | XVB7C21B | 24V Base Direct / Tube & Cover |
|--------------|----------|------------------------------------|
| A1, A7, A11 | XVB7C31 | IO Link Base Direct / Tube & Cover |
| A1, A8, A11 | XVB7C51 | USB Base Direct / Tube & Cover |
| A1, A9, A11 | XVB7C61 | M12 Base Direct / Tube & Cover |
| A1, A10, A11 | XVB7C21M | AC Base Direct / Tube & Cover |
| A2 | XVB7C9S | 2 Tones Buzzer |
| A2 | XVB7C9T | 8 Tones Buzzer |
| A2 | XVB7C9SS | Self-Adjust Sounder 1 Tone |
| | XVB7L2 | Beacon Steady Lens |
| A3 | XVB7L6 | Beacon Flashing Lens |
| A4 | XVB7C9V | Editable Voice Alarm |
| | XVB7C2 | Steady Lens |
| | XVB7C5 | Blinking Lens |
| A5 | XVB7C6 | Flashing Lens |
| | XVB7CR | Rotating Lens |
| | XVB7CM9 | Multi-function Clear lens |
| A12 | XVZ00 | 1/2" NPT Adapter |
| A13 | XVZ02 | Plastic Fixing Plate With Pole |
| A14 | XVZ100 | Alu Ø25mm Pole 100mm Length |
| A15 | XVZ250 | Alu Ø25mm Pole 250mm Length |
| A16 | XVZ400 | Alu Ø25mm Pole 400mm Length |
| A17 | XVZ800 | Alu Ø25mm Pole 800mm Length |
| A18 | XVZ100T | L Bracket Alu Ø25mm Pole 100mm |
| A19 | XVZ250T | L Bracket Alu Ø25mm Pole 250mm |
| A20 | XVZ01 | Plastic Fixing Plate |
| A21 | XVZ11 | Metal Fixing Plate |
| A22 | XVZ06 | Plastic Foldable Bracket |
| A23 | XVZ09 | Plastic Wall Mount Bracket |
| | | |

Product data sheet

XVB7C9S

| A24 | XVZ07 | Side Entry Adapter |
|-----|-------|--------------------|
| A25 | XVZ08 | Magnetic Adapter |

Technical Illustration

Dimensions




Image of product / Alternate images

Alternative













11