

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Cadmium oxide (4.57% in Component Part) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 260°C

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # 1393212-3
[T92S7A22-208](#)

Customers Also Bought



TE Part #2-520403-2
[ULTRA-FAST 187 ASY REC 22-18 TPBR](#)



TE Part #CAT-C339-H85913
[Power Resistors: Aluminum Housed, HSA](#)



TE Part #4-1393248-2
[W33-T4B1Q-10=W33](#)



TE Part #2-1393254-7
[W91-X112-3=M6/M7/M9/W6/W7](#)



TE Part #2176412-1
[5W XSM M/OX 5% 5R1](#)



TE Part #2-1415529-1
[PT320615](#)



TE Part #6-66506-1
[20 DF PIN CONT, SMALL PACK](#)



TE Part #4-1393211-2
[T92P11A22-208](#)

Documents

CAD Files

Customer View Model

[ENG_CVM_CVM_5-1393211-9_F.3d_igs.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_5-1393211-9_F.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_5-1393211-9_F.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

T92 Two-Pole, 30 Amp, PC Board or Panel Mount Relay

English



Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

CQC_CERT_16002142753_C1

English