

SPU30 SERIES

30W Desk Top Switching Power Supplies For I.T.E.

Description:

The SPU30 series of products, DeskTop constructed, AC/DC switching mode power supplies provide 30 Watts of continuous output power. They are ideally suited for use in CRT terminals, disc drive systems, microprocess or based systems, portable equipments and many other applications, all models are designed to meet the safety requirements of UL1950/EN60950 requirements. All units are 100% burned in and tested.



Features:

- Wide Input Voltage 90 to 264 VAC, 47 to 63 Hz
- IEC-320-C14 Input Inlet
- Single and Dual Output
- Output Voltage Available From 3 VDC Thru 50 VDC
- Optional Output Connector (See appendix)
- Input Surge Current, Over Voltage and Over Load protection
- Splash proof
- Class I Insulation
- Two Years Warranty

Safety Approvals:



Electrical Characteristics:

Sym.	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
Vin	Input Voltage		90		264	VAC
Fin	Input Frequency		47		63	Hz
Wo	Output Power Range	Vin=90 to 264VAC	0		30	W
Vo	Output Voltage Range		See rating chart			V
Io	Output Current Range		See rating chart			A
Iil	Input Current (Low Line)	Io=Full load, Vin=115VAC			0.8	A
Iih	Input Current (High Line)	Io=Full load, Vin=230 VAC			0.5	A
Irl	Low Line Inrush Current	Io=Full load, 25 c, Cool start, Vin=115VAC		12	15	A
Irh	High Line Inrush Current	Io=Full load, 25 c, Cool start, Vin=230VAC		26	30	A
Eff	Efficiency	Io=Full Load, Vin=230VAC	65	75	85	%
REG-i	Line Regulation	Io=Full Load		0.5	1	%
REG-o	Load Regulation	Vin=230VAC		3	7	%
OVP	Over Voltage Protection		112		132	%
OCP	Over Current Protection		110		150	%
Ttr	Transient Response	Io=Full Load to Half Load, Vin=100VAC			4	mS
Thold	Hold-Up Time	Io=Full Load, Vin=100VAC	12			mS
Ts	Start Up Time	Io=Full Load, Vin=100VAC	0.3	1	2	S
Vrn	Ripple & Noise (Peak to Peak)	Full Load, Vin=90VAC		1	2	%
Ilk	Safety Ground Leakage Current	Io=Full Load, Vin=240VAC		0.5	0.75	mA
Tc	Temperature Coefficient	All output	-0.04		0.04	%/ c

Environmental :

Sym.	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
Toper	Operating Temperature		0		70	c
Tstg	Storage Temperature		-40		85	c
Hr	Relative Humidity		5		95	%
Pd	Derate linearly from 100% load at 40 c to 50% load at 70 c					

SPU30 SERIES

30W Desk Top Switching Power Supplies For I.T.E.

Safety Specifications:

Sym.	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
Vps	Dielectric Withstanding Voltage for Primary to secondary	Primary to secondary	4242			VDC
Vpg	Dielectric Withstanding Voltage for Primary to ground	Primary to ground	2121			VDC
Ri	Isolation Resistance	Test Voltage = 500VDC	50			MΩ
CISPR	EMI requirements for CISPR-22	Vin=220VAC	B			CLASS
FCC	EMI requirements for FCC PART-15	Vin=110VAC	B			CLASS


Output Voltage And Current Rating Chart (Single Output) :

Model Number	Output Voltage	Output Current	Total Regulation	Maximum Output Power
SPU30-101	3 ~ 5 VDC	5.00 A max	7%	20W
SPU30-102	5 ~ 6 VDC	5.00 ~ 4.16 A	5%	25W
SPU30-103	6 ~ 8 VDC	4.16 ~ 3.12 A	5%	25W
SPU30-104	8 ~ 11 VDC	3.75 ~ 2.72 A	5%	30W
SPU30-105	11 ~ 13 VDC	2.72 ~ 2.30 A	5%	30W
SPU30-106	13 ~ 16 VDC	2.30 ~ 1.87 A	5%	30W
SPU30-107	16 ~ 21 VDC	1.87 ~ 1.42 A	5%	30W
SPU30-108	21 ~ 27 VDC	1.42 ~ 1.11 A	5%	30W
SPU30-109	27 ~ 33 VDC	1.11 ~ 0.90 A	5%	30W
SPU30-110	33 ~ 40 VDC	0.90 ~ 0.75 A	3%	30W
SPU30-111	40 ~ 50 VDC	0.75 ~ 0.60 A	3%	30W

Output Voltage And Current Rating Chart (Multi Output) :

Model Number	Output #1				Output #2				Output #3				Maximum Output Power
	Vonom	Iomin	Iomax	Regmax	Vonom	Iomin	Iomax	Regmax	Vonom	Iomin	Iomax	Regmax	
SPU30-200	+3.3V	0.6A	3A	±5%	+12V	0.20A	1.25A	±10%					24.90W
SPU30-201	+5.0V	0.6A	3A	±5%	+12V	0.20A	1.25A	±10%					30.00W
SPU30-202	+5.0V	0.6A	3A	±5%	+15V	0.20A	1.00A	±10%					30.00W
SPU30-203	+5.0V	0.6A	3A	±5%	+24V	0.124A	0.62A	±10%					30.00W
SPU30-204	+3.3V	0.6A	3A	±5%	+5V	0.30A	1.50A	±10%					17.40W
SPU30-205	+5.0V	0.6A	3A	±5%	+36V	0.10A	0.42A	±10%					30.12W
SPU30-208	+9.0V	0.4A	2A	±5%	-9V	0.20A	1.33A	±10%					30.00W
SPU30-209	+12.0V	0.4A	2A	±5%	-12V	0.10A	0.50A	±10%					30.00W

Mechanical Specifications :



Note:

1. Dimensions are shown in mm.
2. Weight: 230gs approx.
3. Optional output connector: See page Appendix.