




MTA 156

TE Internal #: 3-640427-6

Connector Assembly, Receptacle, Insulation Displacement (IDC),
Wire-to-Board, Tin (Sn), MTA 156, Rectangular Wire & Cable
Connectors & Housings

[View on TE.com >](#)

Connectors > Rectangular Connectors > Standard Rectangular Connectors



Connector Product Type: **Connector Assembly**
Connector & Housing Type: **Receptacle**
Mating Alignment: **Without**
Mating Retention: **With**
Mating Retention Type: **Locking Ramp**

Features

Product Type Features

Compatible With Discrete Wire Type	Stranded
Connector Product Type	Connector Assembly
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Power Positions	6
Number of Positions	6
Number of Rows	1

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Body Features

Cable Exit Angle	90°
------------------	-----



Primary Product Color	Yellow
-----------------------	--------

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	30 µm[.762 µin]
Wire Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	2.03 – 5.08 µm[80 – 200 µin]
Contact Layout	Inline
Contact Base Material	Copper Alloy
Wire Contact Termination Area Plating Thickness	2.03 – 5.08 µm[80 – 200 µin]
Contact Type	Receptacle
Contact Mating Area Plating Material Finish	Matte
Contact Mating Area Plating Material	Tin (Sn)
Contact Retention Within Housing	With
Contact Current Rating (Max)	7 A

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

Strain Relief	With
Panel Mount Feature	Without
Contact Retention Type Within Housing	Locking Lance
Mating Alignment	Without
Mating Retention	With
Mating Retention Type	Locking Ramp
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon
Wire & Cable IDC Installation Type	Closed End
Centerline (Pitch)	3.96 mm[.156 in]

Dimensions

Compatible Insulation Diameter Range	2.41 mm[.095 in]
Connector Height	9.02 mm[.355 in]
Wire Size	20 AWG



Connector Length23.77 mm[.936 in]

Usage Conditions

Operating Temperature Range-55 – 105 °C[-67 – 221 °F]

Operation/Application

Circuit ApplicationPower

Industry Standards

Compatible With Agency/Standards ProductsCSA, UL

UL RatingRecognized

Compatible With Approved Standards ProductsUL E28476

CSA RatingCertified, LR 7189

Glow Wire RatingStandard Part - Not Glow Wire

UL Flammability RatingUL 94V-2

Packaging Features

Packaging Quantity250

Packaging MethodBag & Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EUCompliant

EU ELV Directive 2000/53/ECCompliant

China RoHS 2 Directive MIIT Order No 32, 2016No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006
Current ECHA Candidate List: JUNE 2024 (241)
Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

Halogen Content
Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process CapabilityNot applicable for solder process capability












Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part



numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 3-641439-6 06P MTA156 PST CON ASSY LF	 TE Part # 640389-6 06P MTA156 HDR ASSY SQ R/A F/L	 TE Part # 3-641522-6 06P MTA156 POST CON ASSY ORNG	 TE Part # 58074-1 MTA 50/100/156 MANUAL TOOL FRAME
 TE Part # 641318-3 06CIR MTA156 R/A HDR ASY W/O#3	 TE Part # 58247-3 MTA 156 CRIMP HEAD PRODUCTION RBBN CABLE	 TE Part # 644752-6 06P MTA156 HDR ASSY SQ STR F/L	 TE Part # 3-641435-6 06P MTA156 CONN ASSY ORNG
 TE Part # 3-641437-6 06P MTA156 PSTD CONN ASSY RED	 TE Part # 3-641438-6 06P MTA156 PSTD CONN ASSY WHT	 TE Part # 644749-6 06P MTA156 HDR ASSY STR SQ SN	 TE Part # 3-641524-6 06P MTA156 POST CON ASSY LF
 TE Part # 58247-2 MTA 156 CRIMP HEAD PRODUCTION DISCRETE	 TE Part # 3-644615-6 06P MTA156 POL HDR ASSY LF	 TE Part # 3-641436-6 06P MTA156 PST CONN ASSY LF	 TE Part # 643067-6 06P MTA156 MOLDED COVER



TE Part # 2-647123-6
06P MTA156 SHRD HDR ASSY SQ SN



TE Part # 644753-6
06P MTA156 HDR ASSY RN STR F/L



TE Part # 640385-6
06P MTA156 HDR ASSY SQ R/A



TE Part # 640388-6
06P MTA156 HDR ASSY RN STR F/L

Also in the Series | MTA 156



Connector Caps & Covers(89)




Connector Contacts(4)



Connector Hardware(2)



Insertion & Extraction Tools(1)




PCB Headers & Receptacles(677)



Power Contacts(3)




Rectangular Power Connectors(1178)



Wire-to-Board Headers & Receptacles (677)


Customers Also Bought



TE Part #3-641436-6
06P MTA156 PST CONN ASSY LF



TE Part #3-640427-2
02P MTA156 CONN ASSY 20AWG YEL




TE Part #CAT-C339-H85913
Power Resistors: Aluminum Housed, HSA



TE Part #171551-2
P.G SPADE



TE Part #3-640427-9
09P MTA156 CONN ASSY 20AWG YEL



TE Part #926883-1
UNIVERSAL M-N-L PIN



TE Part #2-6609089-4
16WGA1=F4338



TE Part #7-2151015-2
OCEAN_2.0_APPLICATOR-S-062F125F



Documents

Product Drawings

06P MTA156 CONN ASSY 20AWG YEL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-640427-6_T.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-640427-6_T.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-640427-6_T.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

UL

English