



Relays & Contactors > Electromechanical Relays > Force Guided Relay with 7 contacts



Relay & Contactor Type: **Force-Guided Relay**
Current Type: **DC**
Coil Magnetic System: **Monostable**
Contact Arrangement: **5A (NO) + 2B (NC)**
Contact Current Rating: **6 A**

[All Force Guided Relay with 7 contacts \(8\)](#)

Features

Product Type Features

Relay & Contactor Type	Force-Guided Relay
------------------------	--------------------

Configuration Features

Contact Number of Poles	7
Contact Arrangement	5A (NO) + 2B (NC)

Electrical Characteristics

Contact Limiting Short-Time Current	25 A
Contact Limiting Making Current	25 A
Contact Limiting Continuous Current	6 A
Contact Limiting Breaking Current	6 A
Insulation Initial Dielectric Between Open Contacts	1000 Vrms
Insulation Initial Dielectric Between Adjacent Contacts	2500 Vrms, 4000 Vrms
Contact Switching Voltage (Max)	400 VAC
Contact Switching Load (Min)	10mA @ 5V
Coil Resistance	206 Ω
Contact Current Rating	6 A
Coil Voltage Rating	12 VDC



Contact Voltage Rating	250 VAC
Coil Power Rating DC	.7 W
Insulation Initial Dielectric Between Contacts & Coil	2500 Vrms, 4000 Vrms

Body Features

Product Weight	33 g[1.164 oz]
Enclosure Type	Flux Resistant Automatic Solder Capable

Contact Features

Contact Material	AgSnO2
------------------	--------

Termination Features

Main Termination & Connection Type	Solder Pins
Coil Termination & Connection Type	Solder Pins

Mechanical Attachment

Product Mount Type	Board Mount
--------------------	-------------

Dimensions

Insulation Clearance Between Contact & Coil	5.5 mm[.217 in]
Insulation Creepage Between Contact & Coil	3 mm, 4 mm, 5.5 mm[.217 in]
Product Width	33.8 mm[1.33 in]
Product Length	54.45 mm[2.14 in]
Product Height	10.8 mm[.425 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
Environmental Category of Protection	RTII
Environmental Ambient Temperature (Max)	85 °C[185 °F]

Operation/Application

Current Type	DC
Coil Magnetic System	Monostable

Product Availability

Product Availability	Worldwide
----------------------	-----------

Packaging Features

Packaging Method	Box & Tray
------------------	------------

Other

--	--



Coil Power Rating Class	>.6 – ≤1 W
Contact Current Class	>5 – ≤10 A
Height Class (Mechanical)	10 – 11 mm
Length Class (Mechanical)	50 – 60 mm
Width Class (Mechanical)	30 – 40 mm

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1546556-3
3P,STACKABLE,55 DEG,3.5MM



TE Part # 2-2045880-4
SRL7-523-D012-0010



Also in the Series

SCHRACK SRL7

DC Relays(4)

PCB Relays(4)

Customers Also Bought

TE Part #66103-4
III+ PIN,24-20,30AU/FL,LP

TE Part #66105-4
III+ SKT,24-20,30AU/FL,LP

TE Part #206043-1
RECEPT,SZ 17-14 CPC

TE Part #206044-1
CPC PLUG ASSEMBLY SIZE 17-14

TE Part #1-320551-2
TERMINAL,PIDG R IR 22 8

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2045880-4_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2045880-4_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2045880-4_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



[Force Guided Relay SRL7 flyer](#)

English

[Definitions General Purpose Relays](#)

English

[Force Guided Relay SRL7](#)

English

[Product Specifications](#)

[Definitions General Purpose Relays](#)

English

[Agency Approvals](#)

[VDE Certificate](#)

English