



TE Internal #: ER0075-000
3 Cables, 107 mm [4.21 in] Bolt Hole Centers, 120 mm [4.72 in]
Height (Installed), 1 x M12 Bolt Size, Flat Mount, Hardware,
Grounding & Mounting
[View on TE.com >](#)

Energy & Power > Power Cable Accessories > Hardware, Grounding & Mounting > Cable Cleats made from V0 Flame-Retardant Polymer



Number of Cables to be Mounted: 3
Compatible Cable Diameter Range: 26 – 38 mm [1.02 – 1.5 in]
Bolt Hole Centers: 107 mm [4.21 in]
Height (Installed): 120 mm [4.72 in]
Bolt Size: 1 x M12

[All Cable Cleats made from V0 Flame-Retardant Polymer \(96\)](#)

Features

Configuration Features

Number of Cables to be Mounted	3
--------------------------------	---

Body Features

Bolt Hole Centers	107 mm[4.21 in]
-------------------	-----------------

Mechanical Attachment

Mounting Options	Flat Mount
------------------	------------

Dimensions

Compatible Cable Diameter Range	26 – 38 mm[1.02 – 1.5 in]
Height (Installed)	120 mm[4.72 in]
Bolt Size	1 x M12

Product Availability

Product Availability	Americas, Asia, Australia, New Zealand & Pacific Islands, China, Europe, Middle East & Africa
----------------------	---

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Out of Scope
------------------------------	--------------



EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-OHVT-HS
High Voltage Terminations: Heat Shrink, Self-Support

TE Part # CAT-IXSU
Heat Shrink Terminations: 1C/3C, Indoor

TE Part # CAT-OHVT-C
High Voltage Terminations: Outdoor, Composite

TE Part # CAT-OXSU
Heat Shrinkable Outdoor Termination kits

TE Part # CAT-RPIT
Raychem Plug-In Terminations



TE Part # CAT-RSTI
Screened Separable Connectors 1250 A

TE Part # CAT-CST
Cold Shrink Terminations

TE Part # CAT-ELB
Loadbreak Elbow: 200A, 15 and 25 kV



Customers Also Bought



Documents

Datasheets & Catalog Pages

TREFOIL CABLE CLEATS

English

TREFOIL CABLE CLEATS

German

TREFOIL CABLE CLEATS

TREFOIL CABLE CLEATS

French

TREFOIL CABLE CLEATS

Instruction Sheets

Instruction Sheet (U.S.)

English