



Connectors > Rectangular Connectors > Standard Rectangular Connectors > Rectangular Connectors: Harsh 3-Way Plug



Connector Product Type: **Connector Assembly**

Connector & Housing Type: **Plug**

Mating Alignment: **With**

Mating Alignment Type: **Keyed**

Mating Retention: **With**

[All Rectangular Connectors: Harsh 3-Way Plug \(30\)](#)

Features

Product Type Features

Connector Seal & Plug Type	Triple-Seal
Connector Shell Size	03
Connector Product Type	Connector Assembly
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Insertion Force Type	Normal
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Columns	3
Number of Signal Positions	3
Number of Cavities	3
Number of Power Positions	3
Contacts Preloaded	Yes
Number of Positions	3
Number of Rows	1



Electrical Characteristics

Operating Voltage	400 VAC
-------------------	---------

Body Features

Connector & Keying Code	A
Connector Seal Color	Natural
Seal Material	Fluorosilicone
Cable Exit Angle	180°
Seal Type	Grommet Seal, Interfacial Seal
Primary Product Color	Red

Contact Features

Contact Size	Size 22
Wire Contact Termination Area Plating Material	Gold
Contact Type	Socket
Contact Mating Area Plating Material	Gold (Au)
Contact Retention Within Housing	With
Contact Current Rating (Max)	5 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Mating Alignment	With
Mating Alignment Type	Keyed
Mating Retention	With
Mating Retention Type	Button Latch

Housing Features

Housing Material	Composite
Shell Material	Composite
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
Compatible Insulation Diameter Range	.71 – 1.37 mm[.028 – .054 in]

Usage Conditions

Operating Temperature Range	-55 – 175 °C[-67 – 347 °F]
-----------------------------	----------------------------



Operation/Application

Shielded	No
Circuit Application	Power & Signal

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 245°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Also in the Series | **DEUTSCH 369**




PCB Headers & Receptacles(91)



Rectangular Power Connectors(403)



Standard Rectangular Connectors(358)



Wire-to-Board Headers & Receptacles (91)

Customers Also Bought



TE Part #650071-000
D-436-41




TE Part #1616023-1
B4301 (FAA/PMA)=RELAY




TE Part #ZPF00000000104588
DMC-MD 26 C




TE Part #1996544-1
Seal Boot Ret. Plate Kit, 12 Pos. Quadrax




TE Part #825827-000
202D253-25/225-0




TE Part #ZPF00000000103303
787-8009-00




TE Part #MSDI-0000000000
OPTIMUS MSDI



TE Part #790904N002
D-150-0169CS2902



TE Part #931289N001
SO63-2-9036-20CS2677



TE Part #696863-1
SPLICE,COPALUM BUTT 3/0 13-78

Documents

Product Drawings

369 HARSH 3 WAY PLUG, SKT - BACC65CP1SA

English

369 HARSH 3 WAY PLUG, SKT - BACC65CP1SA

English

CAD Files

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_YD369-HP33-AS00000_AA.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_YD369-HP33-AS00000_AA.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_YD369-HP33-AS00000_AA.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.