


# Lamp With Holder Assembly **multicomp**<sup>PRO</sup>

**RoHS  
Compliant**



## Features

- Designed for ease in circuit board assembly.
- Black case enhance contrast ratio.
- Solid state light source.
- Reliable and rugged.
- 3mm diameter package.

## Applications

- TV set
- Monitor
- Telephone
- Computer
- Circuit board

## Specification

- Chip material : AlInGaP
- Emitted colour : Yellow
- Lens Appearance : Yellow Diffused

## Absolute Maximum Ratings at T<sub>A</sub>=25°C

Parameter	Symbol	Yellow	Unit
Power Dissipation	P <sub>D</sub>	75	mW
Forward Current	I <sub>F</sub>	30	mA
Peak Forward Current*1	I <sub>FP</sub>	50	mA
Reverse Voltage	V <sub>R</sub>	5	V
Operating Temperature	T <sub>opr</sub>	-40°C To +85°C	
Storage Temperature	T <sub>stg</sub>	-40°C To +85°C	
Soldering Temperature	T <sub>sol</sub>	260°C (for 5 seconds)	

\*1Condition for I<sub>FP</sub> is pulse of 1/10 duty and 0.1msec width.

## Electrical / Optical Characteristics at T<sub>A</sub>=25°C

Parameter	Symbol	Test Conditions	Colour	Min.	Typ.	Max	Unit
Forward Voltage	V <sub>F</sub>	I <sub>F</sub> =20mA	Yellow	1.8		2.4	V
Luminous Intensity	I <sub>v</sub>	I <sub>F</sub> =20mA		20		80	mcd
Reverse Current	I <sub>R</sub>	V <sub>R</sub> =1V		—	—	10	μA
Dominate Wave Length	λ <sub>d</sub>	I <sub>F</sub> =20mA		585	590	595	nm
Spectral Line Half-width	Δλ			—	30	—	nm
Viewing Angle	2θ <sub>1/2</sub>			—	70	—	Deg.


Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
sg.element14.com/b/multicomp-pro

**multicomp**<sup>PRO</sup>


# Lamp With Holder Assembly **multicomp**PRO

## Typical Electrical/Optical Characteristics Curves

### Yellow



## Dip Soldering




# Lamp With Holder Assembly **multicomp**PRO

1. Please avoid any external stress applied to the lead-frames and epoxy while the LEDs are at high temperature, especially during soldering
2. DIP soldering and hand soldering should not be done more than one time.
3. After soldering, avoid the epoxy lens from mechanical shock or vibration until the LEDs are back to room temperature.
4. Avoid rapid cooling during temperature ramp-down process
5. Although the soldering condition is recommended above, soldering at the lowest possible temperature is feasible for the LEDs


## Iron Soldering

A: Max: 350°C Within 3 sec. One time only.

B: The products of 3mm without flange, welding condition of flat plate PCB  
Max: 350°C Within 2 sec. One time only



## Dimensions



## Notes

1. Tolerance is  $\pm 0.25\text{mm}$  (0.01") unless otherwise specified.
2. Lead spacing is measured where the leads emerge from the package.
3. Specifications are subject to change without notice.

## Part Number Table

Description	Part Number
1 LED Lamp With Holder, Yellow, 4.6 × 7.4 × 6.5mm, 30mA	BL-33Y-1

Dimensions : Millimetres (Inches)

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
sg.element14.com/b/multicomp-pro

**multicomp**PRO