



Main

Range of product	125 A Frame EDB-EGB-EJB
Product or component type	Miniature circuit-breaker
Device short name	EDB
Module type	E-Frame
Trip unit rating	875 A

Complementary

Line Rated Current	30 A
Maximum operating voltage	480Y/277 V AC
AWG gauge	AWG 12...AWG 6 aluminium AWG 14...AWG 6 copper
Breaking capacity	18 KA 277 V AC 25 KA 240 V AC 18 KA 480Y/277 V AC 25 KA 120 V AC 25 kA 120/240 V AC
Circuit breaker application	HACR rated HID rated
Maximum Depth	4.05 in (102.87 mm)
Electrical connection	Lugs aluminium
Maximum Height	5.66 in (143.76 mm)
Holding current	270 A
Local signalling	Trip indicator
Mounting mode	Bolt-on
Number of poles	3
Number of spaces	3
Number of spaces required	3
Product destination	NF panelboard
Net Weight	4 lb(US) (1.81 kg)
Protection type	Overload Short-circuit
Maximum Width	2.94 in (74.68 mm)
Trip unit technology	Thermal-magnetic
Breaking capacity code	D
Tightening torque	30.09 lbf.in (3.4 N.m) 0.00...0.02 in ² (2.5...16 mm ²) AWG 14...AWG 6)

Environment

Product certifications	CULus
Ambient air temperature for operation	104 °F (40 °C)

Ordering and shipping details

Category	00931 - EDB CIRCUIT BREAKERS
Discount Schedule	DE2
GTIN	00785901875260
Nbr. of units in pkg.	1
Package weight(Lbs)	3.75 lb(US) (1.70 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.50 in (11.43 cm)
Package 1 width	6.10 in (15.494 cm)
Package 1 Length	9.70 in (24.638 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Approximate Dimensions

