



Connectors > RF Connectors > Coax Connectors > BNC RF Connector: Male (Jack), Right Angle



RF Interface: **BNC**

RF Connector Style: **Jack**

RF Connector Mated Outer Diameter (Approximate): **14.53 mm [.572 in]**

Impedance: **50 Ω**

RF Connector Coupling Mechanism: **Bayonet**

[All BNC RF Connector: Male \(Jack\), Right Angle \(30\)](#)

Features

Product Type Features

Connector Shape	Circular
RF Interface	BNC
RF Connector Style	Jack
Connector System	Cable-to-Board, Cable-to-Panel
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

PCB Mount Orientation	Right Angle
Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

--	--



Body Material	PBT
Body Plating Material	Nickel
Contact Features	
RF Connector Center Contact Plating Material	Tin (Sn)
RF Connector Center Contact Material	Phosphor Bronze
Termination Features	
Termination Method to PCB	Through Hole - Solder
Termination Post & Tail Length	4.11 mm[.162 in]
Mechanical Attachment	
Panel Attachment Style	Rear Mount
PCB Mount Retention	With
Panel Mount Feature Type	Lockwasher and Nut
RF Connector Coupling Mechanism	Bayonet
Connector Mounting Type	Panel Mount
RF Contact Captivation Method	Mechanical
Detent	With
Housing Features	
Housing Color	White
Dimensions	
Mounting Post Length	3.48 mm[.137 in]
Profile Height from PCB	15.88 mm[.625 in]
RF Connector Mated Outer Diameter (Approximate)	14.53 mm[.572 in]
Usage Conditions	
Insulation Option	Uninsulated
Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
Operation/Application	
Operating Frequency	4 GHz
Packaging Features	
Packaging Method	Tube
Other	
Grade	Commercial



Additional Features	Hardware Included
Dielectric Material	Polymethylpentene

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) SVHC > Threshold: Pb (3.7% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5330876
BNC PLUG



TE Part # 5221128-1
PLUG,COMMERCIAL BNC



TE Part # 2-221128-3
PLUG,COMMERCIAL BNC



TE Part # 5227426-1
BNC BLKHD RECPT SEALED



TE Part # 413476-2
JACK,DECOUPLER,PCB,VERT,BNC

TE Part # 1-221128-0
PLUG,COMMERCIAL BNC

TE Part # 5413959-3
BNC HEX RT ANG PLUG 50 OHM

TE Part # 2-5221128-3
PLUG,COMMERCIAL BNC

Customers Also Bought

TE Part #1879252-2
RP 2B 4R75 0.1% 15PPM 1K RL

TE Part #1-794606-3
MICRO MNL RPT CNT STRP 30AU LF

TE Part #6-2176389-5
RQ 1206 499R 0.1% 10PPM 5K RL

TE Part #5536385-5
ASSY,PIN,EUROCARD,TYPE B,LEAD-

TE Part #5050865-6
SOCKET,MIN-SPR SN SER-4

TE Part #9-2176390-5
RQ 1206 11K 0.1% 10PPM 5K RL

TE Part #2-2176390-4
RQ 1206 2K0 0.1% 10PPM 5K RL

TE Part #8-1879627-5
H4P 33K 1% 100PPM

TE Part #2-2176391-1
RQ 1206 20K 0.1% 10PPM 5K RL

TE Part #4-2176391-8
RQ 1206 38K3 0.1% 10PPM 5K RL

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_227161-1_AV.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_227161-1_AV.3d_igs.zip

English



Customer View Model

[ENG_CVM_CVM_227161-1_AV.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English

[Product Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English