Specifications



Remote Display, Modicon M171/ M172/M173, flush mounted optimized display

TM173DLED

Main

Range of product	Modicon M171/M172/M173	
Product or component type	Display module	
Display colour	Monochrome	
Supply	External source	

Complementary

Display type	2 x 7-segment LED
Number of key	4
Colour	White
[Us] rated supply voltage	24 V AC/DC
Marking	CE UL
Overvoltage category	II
Height	80.5 mm
Width	34.5 mm
Depth	34.6 mm
Product weight	0.041 kg

Environment

Standards	UL 94 EN 60730-1 EN 60730-2-9
Product certifications	UKCA UL CSA
Ambient air temperature for operation	-2065 °C
Ambient air temperature for storage	-4070 °C
IP degree of protection	IP65
pollution degree	2

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.000 cm

Package 1 Width	9.300 cm
Package 1 Length	13.200 cm
Package 1 Weight	113.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	5
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	754.000 g

Lenvironmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability \geq

${\mathcal Q}$ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	49
Environmental Disclosure	Product Environmental Profile

Use Better

${}^{\mbox{\footnotesize \sc s}}$ Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ae86ba94-4547-4a45-9448-245a31615fc7
REACh Regulation	REACh Declaration


Use Again

♡ Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No

Product datasheet

Dimensions Drawings


Dimensions



Product datasheet

Mounting and Clearance

Mounting



- (1) Insert the device(2) Secure it with the special brackets provided
- (3) Front panel only (tested in accordance with EN 60529 with a steel sheet 2 mm (0.08 in.) thick ±10 %)

Product datasheet

Image of product / Alternate images

Alternative











