




**Part Number :** [190710281](#)  
**Product Description :** InsulKrimp Ring Tongue  
Terminal for 2 AWG Wire  
**Series Number :** 19071  
**Status :** Active  
**Product Category :** Ring and Spade Terminals  
**Engineering Number :** G-675-14X



## Documents & Resources

**Drawings**  
[190710281\\_sd.pdf](#)

**3D Models and Design Files**  
[190710281\\_stp.zip](#)

**Specifications**  
[PS-19902-009-001.pdf](#)  
[PS-19902-011-001.pdf](#)  
[PS-19902-013-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements  
- Eu RoHS  
- REACH SVHC

- Low-Halogen

#### Multiple Part Industry Compliance Documents

- IPC 1752A Class C

- IPC 1752A Class D

- Molex Product Compliance Declaration

- IEC-62474

- chemSHERPA (xml)

#### EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Ring and Spade Terminals
Series	19071
Description	InsulKrimp Ring Tongue Terminal for 2 AWG Wire
Keyword	Ring Terminal, Ring Terminals
Product Name	InsulKrimp
Type	Ring
UPC	800753072558

#### Agency

UL	E32244
----	--------

#### Physical

Barrel Type	Closed
Color - Resin	Red
Flammability	94V-0
Insulation	PVC
Material - Plating Mating	Tin
Net Weight	15.459/g
Packaging Type	Bag
Stud Size	1/4" (M6)
Wire Insulation Diameter	16.50mm max.
Wire Size (AWG)	2

---

## Application Tooling

### Global

Description	Part Number
Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices	<u>192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>192890010</u>
PremiumGrade Hand Crimp Tool for 8-2 AWG Terminals	<u>640013900</u>
Hand Crimp Tool for 2 AWG Insulated Ring Terminals	<u>640017970</u>
Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices	<u>638162000</u>