



Positive Lock

TE Internal #: 2379911-1

Quick Disconnect Receptacle, 18 – 14 AWG, .8 – 2 mm² Wire, 6.35 mm [.25 in] Tab Width, Straight, Brass, Pre-Tin Plating, Reel, F-Crimp, Open Barrel

[View on TE.com >](#)

Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **.8 – 2 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.8 mm [.032 in]**

Features

Product Type Features

Insertion Force	Low
-----------------	-----

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.8 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Pre-Tin
Crimp Type	F-Crimp
Barrel Type	Open

Dimensions

Wire Size	.8 – 2 mm ²
-----------	------------------------

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------



Operating Temperature Range

-40 – 105 °C[-40 – 221 °F]

Packaging Features

Packaging Method	Reel
------------------	------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2498098-1
250 HSG. F-SPRING REC. 12MM 2P
BLK.



TE Part # 2380041-1
250 HSG. F-SPRING REC. 10MM 8MM
4P NAT.



TE Part # 2379907-1
250 HSG REC. F-SPRING 10MM 8MM
3P NAT.

Customers Also Bought



TE Part #2295787-5
STD TIMER PLUG HSG 5P W/EXT. LOCKING

TE Part #2379907-1
250 HSG REC. F-SPRING 10MM 8MM 3P NAT.

TE Part #2390877-7
7P, RAST 5 TAB HEADER, TIN, DIN THV SEL

TE Part #2295787-7
STD TIMER PLUG HSG 7P W/EXT. LOCKING

TE Part #175020-1
250 PL EX REC. 22-18AWG PTBR

TE Part #2390877-5
5P, RAST 5 TAB HEADER, THV

TE Part #2380041-1
250 HSG. F-SPRING REC. 10MM 8MM 4P NAT.

TE Part #42563-2
250 FASTON FLAG REC 12-10 AWG TPBR

TE Part #964203-1
STD PW TIMER CONTACT

TE Part #2358709-3
250 FASTON,TAB,TAPE REEL NO DIMPLE,PTBR

Documents

Product Drawings

250 FSPRING REC. 18-14AWG TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2379911-1_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2379911-1_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2379911-1_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Engineering Report

English

Instruction Sheets

Instruction Sheet (non U.S.)

English

Agency Approvals

VDE Certificate

English