




Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Sealing Cap**
Primary Product Color: **Black**
Primary Product Material: **PA 66/6 GBF**
Operating Temperature (Max): **105 °C [221 °F]**
Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Connector Cover Type	Sealing Cap
----------------------	-------------

Body Features

Seal Material	Silicone
Primary Product Color	Black
Primary Product Material	PA 66/6 GBF

Mechanical Attachment

Component Retention Feature	Chain
-----------------------------	-------

Housing Features

Compatible With Connector Shape	Circular
---------------------------------	----------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Operation/Application

Compatible With Connector Shell Size	28
--------------------------------------	----



Packaging Features

Packaging Method	Carton
Packaging Quantity	100

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | AMP CPC




Circular Connector Backshells & Clamps(1)



Circular Power Connectors(423)




Connector Contacts(6)



Connector Hardware(10)



Power Contacts(6)



Sealing Sleeves(2)

Customers Also Bought



TE Part #ESA202N00340500000
915 PLUG



TE Part #1623729-9
BCHE 17 W 1R0 10%



TE Part #ESB205N00330003000
915 PLUG



TE Part #ESA002N00320001000
615 EXTENSION



TE Part #5-1437567-8
MPG406R=(MSPG) SW PUSHBUTTON



TE Part #1825603-1
BP1532004=Boot,Pushbutton



TE Part #1630019-2
HSC200 10R 5%



TE Part #YDTS26W21-11PNV001
PLUG ASSY



TE Part #ASA035N00610235000
623 PLUG

Documents



Product Drawings

STAUBKAPPE GR 28

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_827155-1_H.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_827155-1_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_827155-1_H.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

UL Report

English