




Energy & Power > Power Systems Connectors > Wedge Connectors



Product Availability: **Americas**
Installation Technology: **Energised Installation, Wedge**
Voltage Class: **≤ 500 kV**

Features

Product Type Features

Power Component Options	Hot Stick Accessories
Installation Technology	Energised Installation, Wedge

Configuration Features

Visual Inspection	Yes
-------------------	-----

Electrical Characteristics

Voltage Class	≤ 500 kV
---------------	----------

Body Features

Compatible Conductor Material	Copper
-------------------------------	--------

Usage Conditions

	32 – 347 °F
--	-------------

Operation/Application

Power Component Application Type	Overhead
----------------------------------	----------

Product Availability

Product Availability	Americas
----------------------	----------

Other

Color Cartridge Required	White
--------------------------	-------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | AMPACT Copper TAP




Wedge Connectors(63)

Customers Also Bought



TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM,
CONNECTOR HOUSING



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #CAT-D48-ST273
DEUTSCH Solid Contacts



TE Part #206070-8
CABLE CLAMP KIT #17



TE Part #DT04-2P
REC, 2P, GRY, N



TE Part #DT06-2S
PLG, 2P, GRY, N



TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT

Documents

Product Drawings

AMPACT CU TAP 250-4

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-275187-0_V.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-275187-0_V.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-275187-0_V.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages

AMPACT COPPER TAPS

English

Product Specifications

Product Specification

English

Tap, AMPACT, Copper

English

Product Specification

English

Agency Approvals

UL Report

English

UL Report

English