



HONEYWELL PART NUMBER	REV	DOCUMENT	CHANGED BY	CHECK
BFLI-AWI-S	A	0018413	NM 18JAN06	RJ



SWITCH WILL
OPERATE BY
MOVING ACTUATOR
IN ANY DIRECTION
EXCEPT DIRECT
PULL



NOTES
1 - 3X 6-32 UNC PRESSURE PLATE TERMINAL SCREWS
2 - FURNISHED UNASSEMBLED

CHARACTERISTICS	CONTACT ARRANGEMENT
OPERATING POSITION:..... 15° MAX OPERATING FORCE:..... 7 OZ MAX	S P D T L162 5A 125, 250, 277 VAC 1/10 HP 250 VAC UL E

DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES X ±	DRAWN NM 16JAN06 CHECK RJ 16JAN06 THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.	Honeywell		
THIRD ANGLE PROJECTION	INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY	TITLE SWITCH, ENCLOSED		
Pro/ENGINEER 3D	SCALE 1:1	SIZE C	TYPE I	DRAWING NAME BFLI-AWI-S
		SHEET 1 OF 1		REV A