




Connectors > Connector Accessories > Connector Caps & Covers



Connector Cover Type: **Strain Relief Cover**

Number of Positions: **36**

Operating Temperature (Max): **105 °C [221 °F]**

Operating Temperature Range: **-55 – 105 °C [-67 – 221 °F]**

Features

Product Type Features

Connector Cover Type	Strain Relief Cover
----------------------	---------------------

Configuration Features

Number of Positions	36
---------------------	----

Mechanical Attachment

Strain Relief	With
---------------	------

Housing Features

Compatible With Connector Shape	D-Shaped
---------------------------------	----------

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]

Packaging Features

Packaging Method	Kit, Package
Packaging Quantity	100

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JUNE 2024 (241)
Candidate List Declared Against: JUNE 2024 (241)
Does not contain REACH SVHC

Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 229974-1
ASSY, PLUG, 50 POS, B SLOT


Also in the Series | CHAMP Docking Connectors

Connector Caps & Covers(28)

Connector Hardware(28)

Connector Strain Relief(2)

Docking Connectors(19)



IDC D-Sub Connectors(55)


Customers Also Bought




TE Part #206705-2
CPC 13-9 FREE HANGING RECPT




TE Part #917804-2
DYNAMIC D-5 TAB CONT. S L/P



TE Part #1-178802-5
DYNAMIC3100S TAB HSG 5P PM X-K




TE Part #3-640601-4
04P MTA156 CONN ASSY 22AWG LF



TE Part #329860
TERMINAL,TERMI-FOIL 16-14



TE Part #CAT-D9934-A83A
Receptacle and Tab Housing: 5.08 or 10.16 mm pitch, 250-600V



TE Part #229975-1
ASSY,RCPT,50POS,B SLOT,BLK HSG



TE Part #5100147-1
Z-PACK/A RAF 110P



TE Part #3-5229912-1
KIT, PLUG, 50 POS, B SLOT

Documents

Product Drawings

90 DEG COVER KIT 36 POS BLK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-552414-1_K.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_3-552414-1_K.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-552414-1_K.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.