

## DATASHEET

### OLS-330 EB525



**Green LED with Epoxy Lens**

#### **Features:**

- Footprint: 3216 (1206)
- Epoxy lens with 40° view angle
- Size: 3.2(L) x 1.6(W) x 1.6(H) mm
- Circuit substrate: Glass Laminated Epoxy
- ROHS and REACH compliant
- Lead-free solderable
- All devices sorted into intensity classes
- Taped in 8 mm blister tape
- Taping: face-up (T) or face-down (TD)

#### **Applications:**

- Sensing
- Illumination

## Typical Electro-Optical Characteristics

Measurement conditions

 $T_{\text{ambient}} = 23\text{ }^{\circ}\text{C}$ ;  $t_{\text{test}} \leq 60\text{ ms}$ 

Parameter	Symbol	Condition	Min	Typ	Max	Unit
Emitting Color			Green			
Forward Voltage	$V_f$	$I_f = 20\text{ mA}$	-		3.6	V
Peak Wavelength	$\lambda_p$	$I_f = 20\text{ mA}$		525		nm
Dominant Wavelength	$\lambda_d$	$I_f = 20\text{ mA}$	520		530	nm
FWHM	$\Delta\lambda$	$I_f = 20\text{ mA}$		20		nm
Luminous intensity	$I_v$	$I_f = 20\text{ mA}$	2500	3000	-	mcd
View Angle	$\theta$	$I_f = 20\text{ mA}$		30		deg.
Reverse Current	$I_R$	$V_R = 5\text{ V}$			10	$\mu\text{A}$

## Maximum Ratings

Parameter	Symbol	Min	Max	Unit
Forward Current	$I_{f, \text{max}}$		30	mA
Forward Current, pulsed	$I_{f, \text{pulse}}$	$f = 1\text{ kHz}, \tau = 1:8$	125	mA
Reverse Voltage	$V_R$		5	V
Power dissipation	$P_d$		110	mW
Thermal Resistance Junction – Solder point	$R_{th_{JS}}$		450	K/W
Operating Temperature	$T_{op}$	-40	+85	$^{\circ}\text{C}$
Storage Temperature	$T_{st}$	-40	+85	$^{\circ}\text{C}$




### WARNING


**ELECTROSTATIC  
SENSITIVE DEVICE**

OBSERVE PRECAUTIONS  
FOR HANDLING


## Typical Performance



**Optical Spectrum**




**Forward Current vs. Forward Voltage**



**Maximum Ratings<sup>(1)</sup>**


(1) Assuming connection to an infinite heatsink



**Radiation Pattern**

## Outline Drawing


Unless otherwise specified, all drawing units are in mm  
Tolerances are: ISO 2768-m




Marking at the Anode side.

## Recommended soldering pad


Unless otherwise specified, all drawing units are in mm unless specified otherwise



## Soldering Profile




Recommended soldering profile for lead free soldering



Recommended soldering profile for solder containing lead

### Manual Soldering:

Maximum soldering iron power, temperature and time 25 W / 300 °C for 3 s.

**Tape And Reel Packaging**

D	Parts/reel
7"	2000

**Packaging**

The reel is sealed in a special plastic bag with integrated ESD protection including a silica dry-pack. Shelf life for sealed bag: 12 months on max. 30 °C and 60% Rh.  
 Floor life: 12 months under max. 30 °C and 60% Rh in a dust free environment.  
 Other bags (i.e. MBB, HIC, Vacuum pack, etc.) available on request.

## Notice

The information describes the type of component and shall not consider as assured characteristics. Terms of delivery and rights to change reserved. The data sheet may change without prior notification; the only valid issue and current revision can be on our website. Due to technical requirements, components may contain dangerous substances.

It is the responsibility of the customer to evaluate and ensure that the use of the products in their specific applications complies with relevant safety standards and regulations. Customers must assess the exposure conditions within their systems and ensure that appropriate measures are taken to prevent exceeding the permissible exposure limits outlined in IEC 62471. EPIGAP OSA Photonics GmbH does not assume liability for any non-compliance arising from the integration or usage of LEDs in customer systems.

Parameters can vary in different applications. The customer must validate all operating parameters for each application. EPIGAP OSA Photonics GmbH does not have the responsibility for the reliability and the degradation behavior of products made with EPIGAP OSA Photonics GmbH diodes as they depend not only on the product itself but also on the operation, manufacturing or design of the final products. The customer is responsible to ensure the long-term stability of the product according to their requirements. If components are used in toys or, life support systems, EPIGAP OSA Photonics GmbH must expressly authorize the use of the components prior to incorporating them into the customer's systems! Packaging: EPIGAP OSA Photonics GmbH uses recyclable packages.

## EPIGAP OSA Photonics GmbH

[www.epigap-osa.de](http://www.epigap-osa.de)

Köpenicker Str.325  
12555 Berlin Germany  
Tel. +49 (0)30 6576 3764  
[sales@epigap-osa.de](mailto:sales@epigap-osa.de)