




Connectors > Automotive Connectors > Automotive Connector Accessories > Automotive Connector Locks & Position Assurance



Primary Product Color: **Natural**

Connector & Contact Retention Accessory Type: **TPA (Terminal Position Assurance)**

Primary Product Material: **PBT GF**

Operating Temperature Range: **-40 – 120 °C [-40 – 248 °F]**

Features

Product Type Features

Connector & Contact Retention Accessory Type	TPA (Terminal Position Assurance)
--	-----------------------------------

Body Features

Primary Product Color	Natural
Primary Product Material	PBT GF

Usage Conditions

Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Method	Box & Carton
Packaging Quantity	800

Other

Serviceable	Yes
-------------	-----

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1703661-1
6POS, MIXED,REC HSG,ASSY




TE Part # CAT-T4827-CH8172
Timer Connector Housing


Also in the Series | Timer Connector System




Automotive Connector Caps & Covers (11)



Automotive Housings(195)



Automotive Terminals(110)



Crimp Terminal Housings(13)



Other Automotive Connector Accessories(1)

PCB Headers & Receptacles(19)

Quick Disconnects(4)

Rectangular Power Connectors(2)

Customers Also Bought

TE Part #CAT-M8793-CH8172
MQS, CONNECTOR HOUSING

TE Part #7798056012
LSTT-9.5-0-50MM

TE Part #1670252-1
70POS,MIXED,TAB HSG

TE Part #284844-2
12 POS MCP HYBRID MALE CONN AS

TE Part #CAT-T4827-CH8172
Timer Connector Housing

TE Part #1801616-1
FUSES HOLDER 10 MINIFUSES

TE Part #1801619-1
RELAY 70A HOLDER

Documents

Product Drawings
RETAINER, 5-6POS. HSG.

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1718879-2_B.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_1718879-2_B.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1718879-2_B.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Product Specifications

5 & 6 pol; JPT -A-/AMP MCP 6.3 Buchsengehause, Zusammenbau, gedichtet

German

Application Specification

German