



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **3**

Centerline (Pitch): **5 mm [.197 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	3
Number of Rows	1

Body Features

Primary Product Color	Natural
-----------------------	---------

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Mechanical Attachment

--	--



Mating Retention Type	Lock
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon
Centerline (Pitch)	5 mm[.197 in]

Usage Conditions

Operating Temperature Range	-25 – 105 °C[-13 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 927155-1
2P MT-EDGE GEH



TE Part # 1703119-1
7POS MT - EDGE HOUSING



TE Part # 1703111-1
6POS MT - EDGE HOUSING



TE Part # 1703129-1
8POS MT - EDGE HOUSING



TE Part # 928017-1
6P MT-EDGE GEH



TE Part # 1703128-1
8POS MT - EDGE HOUSING



TE Part # 1703071-1
2POS MT-EDGE HOUSING



TE Part # 1703114-1
6POS MT - EDGE HOUSING



TE Part # 927157-1
4P MT-EDGE GEH



TE Part # 1703081-1
3POS MT - EDGE HOUSING


Also in the Series | **RAST 5D**



Connector Contacts(12)



Insertion & Extraction Tools(1)



PCB Headers & Receptacles(417)




Power Contacts(3)



Rectangular Power Connectors(481)



Wire-to-Board Connector Assemblies
& Housings(197)



Wire-to-Board Headers & Receptacles
(417)

Also in the Series | **RAST 5 IDC Connectors**



Connector Contacts(12)




Power Contacts(3)



Rectangular Connector Housings(1)



Rectangular Power Connectors(481)



Standard Edge Connectors(31)




Wire-to-Board Connector Assemblies & Housings(197)

Customers Also Bought




TE Part #1-480704-0
06P UMNL PLUG HSG NATL



TE Part #350536-7
UMNL SOK 20-14 .0126 AUNI/BR



TE Part #100495-2
250 FASTON,LIF REC.,16-20 AWG, TPBR



TE Part #5-160432-4
250 FASTON REC 20-16 AWG TPBR



TE Part #182641-1
17-14 CPC SQ FLANGE RECPT RS



TE Part #327735
PG SPD 22-16 COMM 22-18 MIL 6



TE Part #794271-1
03P UMNL INTERFACE SEAL



TE Part #1478764-1
CRIMP KIT 6.0MM



TE Part #770182-1
09P MINI-UMNL ASSY V0 SNNI



TE Part #1379029-3
4POS MQS REC

Documents



CAD Files

Customer View Model

[ENG_CVM_927156-1_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_927156-1_A.2d_dxf.zip](#)

English

3D PDF

English

Customer View Model

[ENG_CVM_927156-1_A.3d_igs.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[RAST Connector System Catalog](#)

English