

Monylon Confort 1

DESCRIPTION

- Industrial protective glove.
- Synthetic filament knitted glove.
- 7 cm stretchable knit wrist.
- 3 sizes available: 6/8, 7/9 and 8/10.
- Trade unit : 10 pairs, 300 pairs in a transit case.

CHARACTERISTICS

- Seamless non-stop process for strength.
- Textile liner made of polyamid thread with a high elasticity.
- Fine gauge for excellent comfort.
- Latex knit wrist to ensure snug fit.
- Ambidextrous shape for double glove life.

PERFORMANCES

- Lint free glove.
- Excellent comfort and dexterity.
- Excellent adaptability to different hand sizes owing to the stretchable yarn.
- In compliance with the standards EN420 (General requirements) and EN388 (Mechanical hazards) by the Institut Français Textile-Habillemt.

APPLICATIONS

- For all kind of assembling, precise or fine handlings requiring a first mechanical protection of the hand and a protection on the product handled.

LIMITATIONS

- Do not use for handling liquids and pointed objects.
- Do not with a rotating machine in which glove may get caught.
- Limited wrist protection on larger sizes.



This glove is certified to comply with the essential requirements of European Directive EEC/89/686 of December 21st, 1989 relative to personal protective equipment submitted to CE type examination issued by a notified laboratory, who certifies the conformity of this glove with the EN standards to which it responds and certifies the performance levels obtained during tests.



EN 420

EN 420

4 Dexterity



2140

EN 388

Mechanical hazards

EN 388

2 Abrasion

1 Cut

4 Tear

0 Puncture

Order codes	
Sizes	Order codes
6-8	7-9
8-10	
Monylon Confort 1	2F21E02000
	2F21E03000
	2F21E04000

