

## MATT BLACK PAINT

**Product Code: MBP**

### PRODUCT DESCRIPTION

A quick drying, high quality, universal spray paint based on alkyd resins. It exhibits excellent coverage and hardness characteristics and is ideally suited for use in manufacturing, repair and for home and workshop use. This paint uses the International RAL classification system.

### CHARACTERISTICS

- \* 100% Ozone Friendly
- \* Excellent coverage & flow
- \* Fast drying with high opacity
- \* Excellent hardness
- \* Very good resistance to water & external conditions
- \* Very good resistance to petrol and other solvents
- \* Excellent adhesion to bare metal

### PREPARATION & APPLICATION

- \* Ensure that surface is dry, smooth and free from dust and grease.
- \* To test, paint a sample panel in advance. Check synthetic and plastic substrates for adhesion and compatibility. For plastics such as PP and EPDM, a primer coat should be applied first.
- \* Shake the spray-can well for at least 2 minutes and at intervals during use.
- \* Spray (holding the aerosol vertical) at a distance of 25-30 cm from the object to be painted. Best results are obtained by applying several thin coats rather than one single thick coat. Wait a few minutes, with a maximum of 30 minutes, between the application of each layer.
- \* After use, clear the valve by spraying with the can inverted
- \* If repainting is necessary, this should be after 24 hours. Drying of the synthetic paint depends on the thickness of the layer and the ambient temperature.

TECHNICAL  
DATA  
SHEET



**Copyright  
Electrolube  
2003**

All information is given in good faith but without warranty. Properties are given as a guide only and should not be taken as a specification. Electrolube cannot be held responsible for the performance of its products within any application determined by the customer, who must satisfy themselves as to the suitability of the product.



## MATT BLACK PAINT – Page 2

### TYPICAL PROPERTIES

Net Volume:	400ml
Net weight:	300g
Gloss:	Angle of 25 to 60°
Coverage:	1.25-1.75 m <sup>2</sup> (layer 25-30μ)
Drying time:	3-5 minutes (dust free) 10-15 mins (touch dry) 2 hrs (fully dry)
Maximum Temperature:	110°C

### PACKAGING

400 ml net aerosol - Black Mat RAL 9005

### ORDER CODE

MBP400

### TECHNICAL DATA SHEET



### Copyright Electrolube 2003

All information is given in good faith but without warranty. Properties are given as a guide only and should not be taken as a specification. Electrolube cannot be held responsible for the performance of its products within any application determined by the customer, who must satisfy themselves as to the suitability of the product.

