



DEUTSCH

TE Internal #: ZPF000000000000486
Pin Contact, Gold (Au), 115 VAC, 115 VDC, Spring Contact
Retention, Size 20 Contact Size, Discrete Wire, 24 – 18 AWG, .25 – 1
mm² Wire, Crimp

[View on TE.com >](#)

Connectors > Contacts > Connector Contacts



Contact Type: **Pin**
Contact Mating Area Plating Material: **Gold (Au)**
Wire Contact Termination Area Plating Material: **Gold**
Operating Voltage: **115 VDC**

Features

Product Type Features

Sealable	Yes
----------	-----

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Electrical Characteristics

Operating Voltage	115 VDC
-------------------	---------

Contact Features

Barrel Type	Closed
Contact Type	Pin
Contact Mating Area Plating Material	Gold (Au)
Wire Contact Termination Area Plating Material	Gold
Contact Retention Within Housing	With
Contact Size	Size 20
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	7.5 A

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Mechanical Attachment



Contact Retention Type Within Housing	Spring
---------------------------------------	--------

Dimensions

Wire Size	.25 – 1 mm ²
-----------	-------------------------

Usage Conditions

Operating Temperature Range	-65 – 150 °C[-85 – 302 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power, Signal & High Speed Data
---------------------	---------------------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (1.2% in alloy) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # ZPF000000000006054
951-00 R 14-15 P 50-090-395

TE Part # ZPF000000000006086
951-00 R 18-32 P 50-090

TE Part # ZPF000000000006109
951-00 R 20-41 P 50-090

TE Part # ZPF000000000006060
951-00 R 14-19 P 50-090

TE Part # ZPF0000000000030093
951-00 R 8-33 P 50-090

TE Part # ZPF000000000006171
951-00 RC 14-19 P 50-090

TE Part # ZPF000000000006030
951-00 R 10-6 P 50-090-1A

TE Part # ZPF0000000000031478
951-06 R 10-6 P 50-090-1A

TE Part # ZPF000000000006029
951-00 R 10-6 P 50-090

TE Part # ZPF000000000006074
951-00 R 16-26 P 50-090

TE Part # ZPF000000000006809
951-06 RC 8-33 P 50-090

TE Part # ZPF0000000000030023
951-00 R 12-10 P 50-090

TE Part # ZPF000000000006118
951-00 R 22-55 P 50-090

TE Part # ZPF000000000006649
951-06 R 22-55 P 50-090

Customers Also Bought

TE Part #ZPF0000000000015210
DMC-M 04-12 SNE

TE Part #ZPF0000000000005890
941-92 A 19-0 PN

TE Part #ZPF0000000000005899
941-92 A 61-0 PN

TE Part #CAT-NTC0049
Satellite (ESA) Surface Mount NTC Sensor





TE Part #ZPF000000000005911
[941-92 B 61](#)



TE Part #ZPF000000000005893
[941-92 A 27-0 PN](#)



TE Part #ZPF000000000020144
[FMJ 11E 20-02 G](#)



TE Part #323676
[TERMINAL,PIDG R 16-14 4](#)

TE Part #GA4K3A354LEVB
[ESAD-ESA DISCRETE-400601304B](#)