



Part Number : 936000212
Product Description : GWconnect EMC - Electromagnetic Compatibility, Metal Cable Gland, with Gasket, for 15.00-20.00mm Cable, M32x1.5 Thread
Series Number : 93600
Status : Active
Product Category : Heavy-Duty Cable Glands
Engineering Number : 7000.7336.0



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	Heavy-Duty Cable Glands
Series	93600
Description	GWconnect EMC - Electromagnetic Compatibility, Metal Cable Gland, with Gasket, for 15.00-20.00mm Cable, M32x1.5 Thread
Cable Gland Type	IP68 - EMC
IP Rating	IP68
Product Name	GWconnect
Standard	EN 50262
UPC	887191842448

Physical

Cable Diameter	15.00-20.00mm
Material - Cable Gland	Brass
Material - Gasket	Elastomer
Material - Plating	Nickel
Net Weight	117.000/g
Packaging Type	Bag
Temperature Range - Operating	-40° to +125°C
Thread Size	M32x1.5
Thread Type	(M) Metric

Use with Part(s)

Description	Part Number
Use With	Where Electromagnetic Compatibility is required, industrial connectors, hoods, housings, sealed enclosures, and boxes