



SAFETY DATA SHEET YELLOW GLOSS PAINT

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

PRODUCT NAME YELLOW GLOSS PAINT

PRODUCT NO. EPJB400

APPLICATION Paint

SUPPLIER ELECTROLUBE. A division of
HK WENTWORTH LTD
KINGSBURY PARK, MIDLAND
ROAD
SWADLINCOTE
DERBYSHIRE, DE11 0AN
UNITED KINGDOM
+44(0)1283 222 111
+44(0)1283 550 177
info@hkw.co.uk

EMERGENCY TELEPHONE +44(0)1283 222 111 between 8.30 am - 5.00pm Mon - Fri

2 HAZARDS IDENTIFICATION

Extremely flammable.

Repeated exposure may cause skin dryness or cracking.

Vapours may cause drowsiness and dizziness.

Irritating to eyes.

Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

CLASSIFICATION Xi;R36. F+;R12. R52/53, R66, R67.

3 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content	Classification
ACETONE	200-662-2	67-64-1	30-60%	F;R11 Xi;R36 R66 R67
PROPANE	200-827-9	74-98-6	10-30%	F+;R12
WHITE SPIRIT	265-151-9	64742-49-0	10-30%	Xn;R65. Xi;R38. N;R51/53.
BUTANE	203-448-7	106-97-8	5-10%	F+;R12
ISOBUTANE	200-857-2	75-28-5	1-5%	F+;R12
XYLENE	215-535-7	1330-20-7	1-5%	R10 Xn;R20/21 Xi;R38

The Full Text for all R-Phrases are Displayed in Section 16

COMPOSITION COMMENTS

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels

4 FIRST-AID MEASURES

NOTES TO THE PHYSICIAN

Treat symptomatically

INHALATION

Move the exposed person to fresh air at once. Get medical attention.

INGESTION

Not relevant.

YELLOW GLOSS PAINT

SKIN CONTACT

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

EYE CONTACT

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

Use: Powder. Dry chemicals, sand, dolomite etc. Water spray, fog or mist.

SPECIAL FIRE FIGHTING PROCEDURES

Move container from fire area if it can be done without risk.

UNUSUAL FIRE & EXPLOSION HAZARDS

Aerosol cans may explode in a fire.

6 ACCIDENTAL RELEASE MEASURES

SPILL CLEAN UP METHODS

Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Ventilate well. Absorb in vermiculite, dry sand or earth and place into containers.

7 HANDLING AND STORAGE

USAGE PRECAUTIONS

Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

STORAGE PRECAUTIONS

Store at moderate temperatures in dry, well ventilated area.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	Std	TWA - 8 hrs		STEL - 15 min		Notes
ACETONE	WEL	500 ppm	1210 mg/m3	1500 ppm	3620 mg/m3	
BUTANE	WEL	600 ppm	1450 mg/m3	750 ppm	1810 mg/m3	
XYLENE	WEL	50 ppm(Sk)	220 mg/m3(Sk)	100 ppm(Sk)	441 mg/m3(Sk)	

WEL = Workplace Exposure Limit.

PROTECTIVE EQUIPMENT



RESPIRATORY EQUIPMENT

In case of inadequate ventilation and work of brief duration, use suitable respiratory equipment.

EYE PROTECTION

Wear approved, tight fitting safety glasses where splashing is probable.

OTHER PROTECTION

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

HYGIENE MEASURES

Wash at the end of each work shift and before eating, smoking and using the toilet. Promptly remove any clothing that becomes contaminated. Use appropriate skin cream to prevent drying of skin. When using do not eat, drink or smoke. DO NOT SMOKE IN WORK AREA!

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE

Aerosol Liquid

YELLOW GLOSS PAINT

COLOUR	Yellow		
ODOUR	Acetone, ketone.		
VOLATILITY DESCRIPTION	Volatile.		
SOLUBILITY	Insoluble in water		
RELATIVE DENSITY	0.750 @ 20 °c	VAPOUR PRESSURE	354.6 kPa
FLAMMABILITY LIMIT - LOWER(%)	0.6		

10 STABILITY AND REACTIVITY

STABILITY

Stable under normal temperature conditions.

CONDITIONS TO AVOID

Avoid heat, flames and other sources of ignition. Avoid contact with acids and alkalis.

11 TOXICOLOGICAL INFORMATION

INHALATION

May cause irritation to the respiratory system. Vapours may cause headache, fatigue, dizziness and nausea. High concentrations of vapours may irritate respiratory system and lead to headache, fatigue, nausea and vomiting.

SKIN CONTACT

Product has a defatting effect on skin. Prolonged contact may cause dryness of the skin. Prolonged or repeated exposure may cause severe irritation.

EYE CONTACT

Irritating to eyes.

Other Health Effects

This substance has no evidence of carcinogenic properties.

ROUTE OF ENTRY

Inhalation.

Name	XYLENE
Toxic Dose 1 - LD 50	4300 mg/kg (oral rat)
Name	ACETONE
Toxic Dose 1 - LD 50	5800 mg/kg (oral rat)
Toxic Dose 2 - LD 50	20,000 mg/kg (oral-rbt)
Toxic Conc. - LC 50	76 ppm/4h (inh-rat)
Name	WHITE SPIRIT
Toxic Dose 1 - LD 50	>5000 mg/kg (oral rat)

12 ECOLOGICAL INFORMATION

ECOTOXICITY

Dangerous for the environment if discharged into watercourses.

Name	XYLENE
LC 50, 96 Hrs, FISH mg/l	2.6-8.4
EC 50, 48 Hrs, DAPHNIA, mg/l	1.0-4.7
Name	ACETONE
LC 50, 96 Hrs, FISH mg/l	8300
EC 50, 48 Hrs, DAPHNIA, mg/l	12600
Degradability	
The product is easily biodegradable.	
Name	WHITE SPIRIT

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

Empty containers must not be burned because of explosion hazard. Dispose of waste and residues in accordance with local authority requirements.

14 TRANSPORT INFORMATION

YELLOW GLOSS PAINT



UK ROAD CLASS	2		
PROPER SHIPPING NAME	AEROSOLS		
UN NO. ROAD	1950	UK ROAD PACK GR.	N/A
ADR CLASS NO.	2	ADR CLASS	Class 2: Gases
ADR PACK GROUP	N/A	ADR LABEL NO.	2.1
CEFIC TEC(R) NO.	20G5F	RID CLASS NO.	2
RID PACK GROUP	N/A	UN NO. SEA	1950
IMDG CLASS	2.1	IMDG PACK GR.	N/A
EMS	F-D, S-U	MFAG	See Guide
MARINE POLLUTANT	No.	UN NO. AIR	1950
AIR CLASS	2.1	AIR PACK GR.	N/A

15 REGULATORY INFORMATION

SYMBOLS



Irritant



Extremely Flammable

RISK PHRASES

R12	Extremely flammable.
R36	Irritating to eyes.
R52/53	Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R66	Repeated exposure may cause skin dryness or cracking.
R67	Vapours may cause drowsiness and dizziness.

SAFETY PHRASES

A1	Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.
A2	Do not spray on a naked flame or any incandescent material.
S2	Keep out of the reach of children
S16	Keep away from sources of ignition - No smoking.
S23	Do not breathe vapour/spray.
S25	Avoid contact with eyes.
S38	In case of insufficient ventilation, wear suitable respiratory equipment.

UK REGULATORY REFERENCES

Chemicals (Hazard Information & Packaging) Regulations.

The Control of Substances Hazardous to Health Regulations 1988.

ENVIRONMENTAL LISTING

Rivers (Prevention of Pollution) Act 1961. Control of Pollution Act 1974.

EU DIRECTIVES

System of specific information relating to Dangerous Preparations. 2001/58/EC.

Dangerous Substance Directive 67/548/EEC.

Dangerous Preparations Directive 1999/45/EC.

YELLOW GLOSS PAINT

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

GUIDANCE NOTES

Workplace Exposure Limits EH40.

16 OTHER INFORMATION**REVISION COMMENTS**

Revised in accordance with CHIP3 and EU Directives 1999/45/EC and 2001/58/EC

ISSUED BY

Helen O'Reilly

REVISION DATE SEPTEMBER 2008

REV. NO./REPL. SDS 3

GENERATED

SDS NO. 11025

RISK PHRASES IN FULL

R10	Flammable.
R11	Highly flammable.
R12	Extremely flammable.
R20/21	Harmful by inhalation and in contact with skin.
R36	Irritating to eyes.
R38	Irritating to skin.
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R65	Harmful: may cause lung damage if swallowed.
R66	Repeated exposure may cause skin dryness or cracking.
R67	Vapours may cause drowsiness and dizziness.

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.