

EC Aura II

ebmpapst

engineering a better life




EC Aura II

Circulating fan offering an energy efficient low noise solution to traditional temporary cooling solutions.

- Robust polyethylene moulding.
- Impeller of high-quality composite material, manufactured in an injection moulding process.
- Heavy duty powder coated wheeled frame for effortlessly positioning.
- Infinitely variable speed control.
- 180 adjustable tilt angle.
- Maintenance-free IP40 motor.
- Supplied with 230VAC Schuko type plug with converter for UK socket.
- The EC Aura 2 is RoHS compliant and CE marked.

	Supply voltage	Frequency	Maximum airflow	Max. Current draw	Max. Power input	Sound pressure @3m	Mass	Max. Ambient temperature	Air velocity @ 5m	Air velocity @ 10m	Air velocity @ 15m	Air velocity @ 20m
Part number	VAC	Hz	m³/h	Amps	kW	dB(A)	kg	°C	m/s	m/s	m/s	m/s
EC Aura II	230	50/60	8520	2.9	0.65	67	27	+60	3.5	1.6	1.1	0.8



www.ebmpapst.com

ebm**papst**

engineering a better life

ebm papst UK
Chelmsford Business Park,
CM2 5EZ, United Kingdom
+44 (0) 1245 456530
info@uk.ebmpapst.com