




**Part Number :** [1300630012](#)  
**Product Description :** BradPower D-Size (1 3/8"-M35) Single-Ended Cordset, 4 Poles, Male (Straight) to Pigtail with Alternate Key, 10 AWG, PVC Cable, 2.0m (6.56') Length  
**Series Number :** 130063  
**Status :** Obsolete  
**Product Category :** Circular Industrial Cordsets  
**Engineering Number :** C04106A48M020



---

## Documents & Resources

---

### Product Environment Compliance

#### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

#### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

#### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Obsolete
Category	Circular Industrial Cordsets
Series	130063
Description	BradPower D-Size (1 3/8"-M35) Single-Ended Cordset, 4 Poles, Male (Straight) to Pigtail with Alternate Key, 10 AWG, PVC Cable, 2.0m (6.56') Length
IP Rating	IP67
Product Name	BradPower D-Size
Protocol	EtherNet
Type	Single Ended
UPC	78678807022

#### Agency

UL	E258922
----	---------

#### Electrical

Current - Maximum per Contact	25.0A
Voltage - Maximum	600V AC/DC

#### Physical

Cable Diameter	19.81mm (.780")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Gray
Connector End A	BradPower D-Size (1 3/8"-M35)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	Alternate
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Contact	Copper Alloy
Material - Coupling Nut	Anodized Aluminum
Material - Plating Mating	Gold

Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-20° to +90°C
Wire/Cable Type	STOOW, TC-ER Direct Burial
Wire Size (AWG)	10

---

This document was generated on Mar 26, 2025