




**Part Number :** [622018778](#)

**Product Description :** Press-in-Tool for Daughter Card Signal Module, 2-Pair by 10-Column Assemblies

**Series Number :** 207123

**Status :** Obsolete

**Product Category :** Application Tooling Accessories



---

## Documents & Resources

### Tooling Specifications

[ATS-622018778-001.pdf](#)

[TM-622018799-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Contained per D(2021)4569-DC (8 July 2021)
EU RoHS	Compliant per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Obsolete
Category	Application Tooling Accessories
Series	207123
Description	Press-in-Tool for Daughter Card Signal Module, 2-Pair by 10-Column Assemblies
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	Impact
Tool Type	Press-Fit Insertion Tool
UPC	884982113862
Warranty Disclaimer	<p>CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.</p>

---

### Applicable Parts

Description	Part Number
Impact 100 Ohm 2 Pair Right-Angle Male Header, Unguided, Open Endwall, 10 Columns, 60 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.46mm, Lead-Free	<u>764501104</u>

Impact 100 Ohm 2 Pair Right-Angle Male Header, Unguided, Open Endwall, 10 Columns, 60 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>764501107</u>
Impact 100 Ohm 2 Pair Right-Angle Male Header, Unguided, Open Endwall, 10 Columns, 60 Circuits, Pin Length 5.50, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>764501108</u>
Impact 100 Ohm 2 Pair Right-Angle Male Header, Unguided, Left Endwall, 10 Columns, 60 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>764501117</u>
Impact 100 Ohm 2 Pair Right-Angle Male Header, Unguided, Dual Endwall, 10 Columns, 60 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>764501127</u>
Impact 100 Ohm 2 Pair Right-Angle Male Header, Unguided, Right Endwall, 10 Columns, 60 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>764501137</u>
Impact 100 Ohm 2 Pair Right-Angle Male Header, Left Guided, Open Endwall, 10 Columns, 60 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>764503107</u>
Impact 100 Ohm 2 Pair Right-Angle Male Header, Left Guided, Open Endwall, 10 Columns, 60 Circuits, Pin Length 5.50mm,, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>764503108</u>
Impact 100 Ohm 2 Pair Right-Angle Male Header, Right Guided, Open Endwall, 10 Columns, 60 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>764505107</u>
Impact 100 Ohm 2 Pair Right-Angle Male Header, Right Guided, Open Endwall, 10 Columns, 60 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>764505108</u>

Impact 100 Ohm 2 Pair Right-Angle Male Header, Left Guided, Right Endwall, 10 Columns, 60 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>764507107</u>
Impact 100 Ohm 2 Pair Right-Angle Male Header, Left Guided, Right Endwall, 10 Columns, 60 Circuits, Pin Length 5.50mm,, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>764507108</u>
Impact 100 Ohm 2 Pair Right-Angle Male Header, Right Guided, Left Endwall, 10 Columns, 60 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead Free	<u>764509107</u>
Impact 100 Ohm 2 Pair Right-Angle Daughtercard Receptacle, Unguided, 10 Columns, 60 Circuits, Plated Through Hole Dimension 0.46mm, Lead-Free	<u>764601010</u>
Impact 100 Ohm 2 Pair Right-Angle Daughtercard Receptacle, Unguided, 10 Columns, 60 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>764601020</u>
Impact 100 Ohm 2 Pair Right-Angle Daughtercard Receptacle, Left Guided, 10 Columns, 60 Circuits, Plated Through Hole Dimension 0.46mm, Lead-Free	<u>764603010</u>
Impact 100 Ohm 2 Pair Right-Angle Daughtercard Receptacle, Left Guided, 10 Columns, 60 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>764603020</u>
Impact 100 Ohm 2 Pair Right-Angle Daughtercard Receptacle, Right Guided, 10 Columns, 60 Circuits, Plated Through Hole Dimension 0.46mm, Lead-Free	<u>764605010</u>
Impact 100 Ohm 2 Pair Right-Angle Daughtercard Receptacle, Right Guided, 10 Columns, 60 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free	<u>764605020</u>