




Wire Protection & Management > Cable Glands > Plastic Cable Glands Without Locknut



Cable Gland Product Type: **Cable Gland**
Cable Gland & Accessory Style: **Standard Threaded**
Primary Product Material: **PA 6**
Clamping Diameter Range: **11 – 17 mm**
Primary Product Color: **Gray**

[All Plastic Cable Glands Without Locknut \(240\)](#)

Features

Product Type Features

Cable Gland Product Type	Cable Gland
Cable Gland & Accessory Style	Standard Threaded
Sealable	Yes

Body Features

Primary Product Material	PA 6
Primary Product Color	Gray

Dimensions

Clamping Diameter Range	11 – 17 mm
Outer Thread Size	M25 x 1.5
Thread Length	8 mm

Usage Conditions

Operating Temperature Range	-20 – 100 °C[-4 – 212 °F]
-----------------------------	---------------------------

Industry Standards



UL Flammability Rating	UL 94V-2
IP Rating	IP68

Packaging Features

Packaging Method	Bag
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought





TE Part #2-1393122-0
KHAU-17A11-120=KH



TE Part #5-747905-5
9 Rcpt Solder Cup, 30 gold, Ro



TE Part #7-1393117-8
KUP-14A15-120=KU-



TE Part #2-1393115-6
KUL-11A15S-120=KU



TE Part #1SNG607011R0000
EP-LN-M25-GR-A



TE Part #1-206062-6
CABLE CLAMP KIT #11



TE Part #1SNG601056R0000
EP-SG-M20-GR-C



TE Part #130094
PIDG RING



TE Part #4-1609134-8
20ESRMC2=F8278



TE Part #5227161-2
RTANG JK W/MTG PINS, BNC PCB

Documents

Product Drawings
EP-SG-M25-GR-E

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_1SNG601089R0000_A.2d_dxf.zip

English

Customer View Model
ENG_CVM_CVM_1SNG601089R0000_A.3d_igs.zip

English

Customer View Model
ENG_CVM_CVM_1SNG601089R0000_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



Catalog - ENTRELEC Cable Glands

English

Agency Approvals

UL

English

UL

English