

RG58 Coaxial Cable

multicompPRO

Construction



Item	Material	Diameter	
		(Inch)	(mm)
Inner Conductor	Stranded; Tinned Copper	19/0.0071 ±0.002	19/0.18 ±0.05
Dielectric	Solid PE	0.116 ±0.004	2.95 ±0.1
Shield	95% Tinned Copper Braid	0.14 ±0.004	3.55 ±0.1
Jacket	LSZH	0.195 ±0.004	4.95 ±0.1

Electrical Characteristics

Impedance	: 50Ω ±2Ω
Capacitance	: 101pF/m
Velocity of Propagation	: 66%
Max. Operating Frequency	: 1GHz
Max. Operating Voltage	: 1900Vrms
Corona Extinction Voltage	: 1900Vrms
Voltage Withstand	: 5000Vrms
Spark Test	: 5000Vrms
Operating Temp. Range	: -40°C to +85°C

Attenuation (@20°C)

Frequency (MHz)	Max. Attenuation (dB/100ft)	Max. Attenuation (dB/100m)
10	1.5	4.9
50	3.3	10.9
100	4.7	15.5
200	7.5	24.5
400	10.6	34.8
600	12.1	39.6
860	17.2	56.4
1000	18.4	60.5

Part Number Table

Description	Length	Part Number
Coaxial Cable, RG58, LSZH, Black	Per Meter or 100 Meter	RG58

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO