

Accessories

SE-CS30 SERIES CURRENT TRANSFORMER

Current Sensor



Ordering Information

ORDERING NUMBER	WINDOW SIZE, ID	WEIGHT
SE-CS30-26	26 mm (1.0")	0.5 kg (1.0 lb)
SE-CS30-70	70 mm (2.8")	1.2 kg (2.5 lb)
SE-CS30-4	95 mm (3.7")	1.3 kg (3.0 lb)
SE-CS30-5	130 mm (5.1")	2.1 kg (4.6 lb)
SE-CS30-8	200 mm (7.9")	4.3 kg (9.4 lb)

Description

The SE-CS30 series is a sensitive nickel-core current transformer used with Littelfuse relays to detect low levels of earth-leakage current.

Accessories



CBLTP
Twisted-pair wire for connection to CT.
Order in desired length in meters.


Specifications

Turns Ratio	600:1
Current Rating	30:0.05 A
Accuracy	3% @ 0.06 VA
Frequency	50-400 Hz
Insulation Level	600 V
Operating Temperature	-55 to 60°C (-67 to 140°F)

Application
FPU-32, FPS, MPU-32, MPS, PGR-6100, PGR-6101, SE-330, SE-701, SE-704

Certification
CSA, UL, CE



Compliance
RoHS, IEC 60044-1



Accessories




SE-CS30 SERIES CURRENT TRANSFORMER

Dimensions and Mounting Diagram SE-CS30-26



NOTES:



1. DIMENSIONS IN MILLIMETERS (INCHES)
2. MOUNTING SCREWS: M4 OR 8-32
3. TOLERANCE: +/- 1 (0.039)
4. RoHS COMPLIANT
5. EN 60044-1 COMPLIANT



Accessories




SE-CS30 SERIES CURRENT TRANSFORMER

Dimensions and Mounting Diagram SE-CS30-70




NOTES:

1. DIMENSIONS IN MILLIMETERS (INCHES)
2. MOUNTING SCREWS: M4 OR 8-32
3. TOLERANCE: +/- 1 (0.039)
4. RoHS COMPLIANT
5. EN 60044-1 COMPLIANT





SE-CS30 SERIES CURRENT TRANSFORMER

Dimensions and Mounting Diagram




TOP (COVER REMOVED)



BOTTOM

NOTES:

1. DIMENSIONS IN MILLIMETERS (INCHES)
2. MOUNTING SCREWS: M5 OR 10-32
3. RoHS COMPLIANT
4. CE COMPLIANT



MOUNTING DETAIL

	DIMENSIONS		
	SE-CS30-4	SE-CS30-5	SE-CS30-8
A	95.0 (3.74)	130.0 (5.12)	200.0 (7.87)
B	175.0 (6.89)	218.0 (8.78)	309.0 (12.17)
C	158.0 (6.22)	203.0 (7.99)	290.5 (11.44)
D	141.0 (5.55)	178.0 (7.01)	267.5 (10.50)
E	82.0 (3.22)	103.5 (4.07)	150.0 (5.90)
F	32.0 (1.26)	32.0 (1.26)	34.0 (1.34)
G	17.5 (0.69)	11.0 (0.43)	11.0 (0.43)
H	15.0 (0.59)	13.3 (0.52)	13.3 (0.52)
I	33.0 (1.30)	34.0 (1.34)	43.0 (1.69)
J	9.0 (0.35)	11.0 (0.43)	11.5 (0.45)
K	40.0 (1.57)	40.0 (1.57)	50.0 (1.97)
L	5.3 (0.21)	7.0 (0.28)	7.0 (0.28)

Disclaimer Notice – Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/product-disclaimer.