



Application Tooling > Hand Crimping Tools



Tool Grade: **Premium Crimp Tooling**
Ratchet Configuration: **Not Releasable, Not Adjustable**
Die Sets Type: **Fixed In Tool**
Specification Type: **MIL Spec, TE Product Specification (114-)**
TE Certification: **Yes – Certificate Included**

Features

Other

Crimp Form-Wire Barrel Type	Closed Barrel - Confined Crescent
Tool Grade	Premium Crimp Tooling
Ratchet Configuration	Not Releasable, Not Adjustable
Die Sets Type	Fixed In Tool
Specification Type	MIL Spec, TE Product Specification (114-)
TE Certification	Yes – Certificate Included
Power Technology Type	Battery, Manual
Tooling Type	T Head Hand Tool

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)




EU RoHS Directive 2011/65/EU	Out of Scope
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	Not reviewed for China RoHS compliance
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC

Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 321019 TERMINAL,PIDG R 26-22 6	 TE Part # 321017 TERMINAL,PIDG R 26-22 4	 TE Part # 323011 TERMINAL,PIDG R SLTD 26-22 6	 TE Part # 696426-1 SPLICE BUTT PVF2 PIDG 24-20
 TE Part # CAT-P592-F614 PIDG Flanged Spade Tongue Terminals	 TE Part # 321015 TERMINAL,PIDG R 26-22 2	 TE Part # 321035 PIDG 26-22 SPADE #4 STUD	 TE Part # 321020 TERMINAL,PIDG R 26-22 6
 TE Part # CAT-P592-L853 PIDG Long Spring Spade Tongue Terminals	 TE Part # 53809-2 TERMINAL,PIDG PVF2 R 24-20 6	 TE Part # 321021 PIDG RING (26-22)	 TE Part # CAT-P592-B98 PIDG Butt Splices






TE Part # 2-525446-3
[SLIP GAUGE, HANDTOOL](#)




TE Part # CAT-P592-R472A
[PIDG Ring Tongue Terminals](#)



TE Part # 52924
[TERMINAL,PIDG SPR SPD 26-22 6](#)

Customers Also Bought




TE Part #610217-000
[55PC6003-20-2/6-9CS2502](#)




TE Part #M15570-20
[TOOL INS/REM](#)




TE Part #650124-000
[D-436-94](#)




TE Part #160772-3
[110 FASTON, REC., 26-22 AWG, TPBR](#)



TE Part #59239-4
[HHHT PIDG PG 12-10 ASSY](#)




TE Part #46988
[DAHT STRATO 16-14 ASSY](#)



TE Part #806234-000
[202C621-50-0](#)



TE Part #206486-2
[CPC RECPT ASSEMBLY SIZE 11-9](#)



TE Part #480029-000
[222D152-3/86-0](#)



TE Part #062146-000
[TMS-SCE-2-2.0-6](#)

Documents

Product Drawings

[T-HEAD PIDG PG SH 26-20 ASSY](#)

English

Datasheets & Catalog Pages

[Bottoming Dies](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)



English

[Instruction Sheet \(U.S.\)](#)

English