



FEATURES

- High Power Density
- Over 500,000 cycle life (semi-permanent)
- 2 units serially connected to provide 6.0V products
- RoHS compliant
- Long-term reliability improved at high temperature and humidity



Drawing



D = 8.5mm, d=0.6mm

TYPE	I	O	H
P	4.5	12.9	8.5

(Unit : mm)

SPECIFICATION

ITEM		CHARACTERISTICS						
Product series		EDLC 2 SERIAL MODULE						
Rated Voltage (V _R)		6.0V						
Operating Temperature		-40 ~ +65°C						
Capacitance Tolerance		-10 ~ +30%						
High Temperature Load Life		After 1,000 hours at V _R loaded under +65°C, capacitors meet the following criteria.						
		Capacitance Change		≤ 30% of initial value				
		ESR		≤ 2 times of specified value				
		85°C Temperature		Max. 4.8V				
Cycle Life Characteristics	Cycle	Over 500,000						
	ΔC	≤ 30% of initial value						
	ESR	≤ 2 times of specified value						
	Method	Cycle of Charge/discharge from V _R to 1/2V _R						
Shelf Life		3 Years						
		No Electrical Charge, Temperature below 25°C (ΔC : ≤ 10% of initial value / ΔESR : ≤ 50% of specified value)						
Part Number	Rated Voltage (V)	Capacitance (F)	ESR (mΩ)		Max. Current (A)	Leakage Current (mA, 72hr)		Size (mm)
			AC(1kHz)	DC		@5.4V	@6.0V	
WEC 6R0 155 QG	6.0	1.5	155	255	3.5	0.007	0.010	8.5x17x22

* Max. Current : 1 sec. discharge to 1/2V_R

* When do module more than 2 series, please fully discharge over 1 hour first, then assemble right after within 1 hour.