



Heat Shrink Tubing > LSTT2 Heat Shrink Tubing



Tubing Product Type: **Heat Shrink Tubing**

Primary Product Color: **White**

Shrink Ratio: **2:1**

Wall Type: **Single Wall**

Recovered Inside Diameter (Max): **12.7 mm [.5 in]**

[All LSTT2 Heat Shrink Tubing \(41\)](#)

Features

Product Type Features

Tubing Product Type	Heat Shrink Tubing
Wall Type	Single Wall

Electrical Characteristics

Operating Voltage (Max)	.6 kV
-------------------------	-------

Body Features

Fluid Type	Antifreeze, Battery Acid, Diesel Fuel, Gasoline, Hydraulic Fluid, Lubricating Oil, Water
Primary Product Color	White
Shrink Ratio	2:1
Primary Product Material	Irradiated Modified Polyolefin
Flexibility	Very Flexible

Dimensions

Recovered Wall Thickness (Nominal)	.95 mm[.037 in]
Recovered Wall Thickness (Tolerance)	.15 mm[.006 in]
Recovered Inside Diameter (Max)	12.7 mm[.5 in]
Expanded Inside Diameter (Min)	25.4 mm[1 in]
Tubing Size Range	12.7 – 25.4 mm[.5 – 1 in]



Usage Conditions

Shrink Temperature (Min)	65 °C
Tubing Flammability Type	Non-Flame-Retardant
Operating Temperature Range	-40 – 125 °C
Recovery Temperature	110 °C

Operation/Application

Mechanical Resistance	Mechanical Damage
-----------------------	-------------------

Product Availability

Applicable Region	Global
-------------------	--------

Packaging Features

Packaging Method	Reel
------------------	------

Other

Meets Low Outgassing Requirements	No
Product Source	Czech Republic

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits




as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # EG1114-000  
CV1981-ST-230V1600W-EU

Also in the Series | RAYCHEM LSTT




Heat Shrink Tubing(139)



Single Wall Tubing(139)


Customers Also Bought



TE Part #55845-1  
#8 PRE-INSUL SEALED SPLICE



TE Part #1776695-1  
Strain Relief, D5200, Dynamic



TE Part #1-2373376-0  
10P,2MM,SHRD HDR,DRV,T,SMD,0.1 AU,TB



TE Part #2333393-7  
QSFP 25GIG 30AWG 3 METER



TE Part #3-644426-7  
07P MTA100 CONN ASSY W/O#5



TE Part #1986185-1  
Strain Relief,6 Posn,D5200 Dynamic. 2



TE Part #1986186-1  
Strain Relief,20 Posn,D3000 Dynamic, 2



TE Part #52430-3  
TERMINAL,PIDG SPR SPD 12-10 6



Documents

Product Drawings

LSTT-25.4-9-SP

English

Datasheets & Catalog Pages

LSTT Pages from 9-1773447-9

English

Product Specifications

Application Specification

English